



# QC894

<b>Technology</b>	IP HD
<b>Channels</b>	4
<b>Recording Resolution</b>	1080p/720p
<b>Hard Drive</b>	Supports 1 HDD up to 6TB
<b>Remote Monitoring</b>	128 Simultaneous Users
<b>Compatibility</b>	Mac and PC
<b>Connects With</b>	QC IP Cameras
<b>Monitor Connections</b>	HDMI , VGA



## NVR

Video Compression	H.264+/ H.264
Live Display Resolution	1080P/1280x1024/1280x1024/1280x768
Display Modes	1, 4,
Languages	English, Spanish, French

## RECORDING RESOLUTION OPTIONS

1080p Resolution	1920 x 1080 pixels
720p Resolution	1280 x 720 pixels

## RECORDING MODES

Recording Modes	Manual, Time Schedule, Motion Detection, Sensor
Backup Modes	PC, USB Flash, Hard Drive

## PLAYBACK ON NVR

Playback Speed	1080p at 30 FPS per channel	120 FPS Total
	720p at 30 FPS per channel	120 FPS Total
Number of Channels	4 Simultaneous Local Playback	

## REMOTE MONITORING

Scan N'View	Yes
Dual Stream	D1 and CIF
Simultaneous Users	128

## COMPATIBILITY

Software Support	QC View
Mobile Support	iPhone, iPad, Android
Computer Support	Window XP, Windows Vista, Windows 7,8,10 Mac OS 10.7+

## VIDEO, AUDIO & ALARM PORTS

Video In	4 POE
Video Out	HDMI (2.0), VGA
Alarm In	N/A
Alarm Out	N/A
Audio In	1 RCA, for two way talk
Audio Out	1 RCA

## COMMUNICATION PORTS

Network	RJ45 10/100Mbps
USB	1 Rear USB 2.0, 1 Front USB 2.0
eSATA	None

## ACCESSORIES

Control	USB Mouse
Connectors/Cables	HDMI Cable
Mounting Hardware	Screws for Hard Drives
Other	Quick Start Guide

## QC894 Contd.

### HARD DRIVES

Maximum Size	6TB
Number Supported	1

### POWER

Power Supply	DC 48 V/1.25 A
Power Consumption	<4 W (w/o HD)

### PTZ

PTZ Support	Through network ethernet cable
-------------	--------------------------------

### PHYSICAL

Weight	1.76 lbs
Dimensions	10.2" x 8.9" x 1.9"
Operating Temperature	14°F - 131°F

