

VM-4H2

1:4 4K HDR HDMI DA

| HDMI | HDCP Compliant | 4K/60 UHD (4:4:4) | 4K HDR



VM-4H2 is a 1:4 distribution amplifier for up to 4K HDR, HDMI 2.0 signals that comply with HDCP 2.2 content protection standard. The unit takes one HDMI input, equalizes and reclocks the signal and distributes it to four identical outputs

FEATURES

Max. Data Rate - 17.82Gbps (5.94Gbps per graphic channel)

Max. Resolution - 4K@60Hz (4:4:4)

HDMI Signal Transmission - HDR, HDMI 2.0 and HDCP 2.2 compliant signal, supporting deep color, x.v.Color™, lip sync, 7.1 PCM, Dolby TrueHD, DTS-HD, CEC (OUT 1 only), 2K, 4K, and 3D Intelligent EDID Handling - Use connected display EDID or default EDID, with EDID lock and RGB-force options, to ensure proper operation of HDMI source and display systems

Kramer Equalization & re-Klocking™ Technology - Rebuilds the digital signal to travel longer distances

Force RGB - When the display lacks YCbCr capabilities, the user can force native delivery of the RGB color format in HDMI content to improve picture quality

Selectable HDCP Authorization - Allows the user to control the appearance of an HDCP or non-HDCP input to the source to permit delivery of protection-free content, such as personal clips and charts, without HDCP encryption. HDCP protected content is not passed in non-HDCP mode

Field Maintenance - RS-232 connection for simple field firmware upgrade, status indicators for HDMI input and output connected signals, and power indicator, for ease of maintenance and troubleshooting

Easy Installation - Compact Mega TOOLS™ fan-less enclosure for over-ceiling mounting, or side-by-side rack mounting



TECHNICAL SPECIFICATIONS

INPUT: 1 HDMI connector

OUTPUTS: 4 HDMI connectors

PORT:1 RS-232 for firmware upgrade

MAX. DATA RATE: 17.82Gbps (5.94Gbps per graphic channel) supporting resolutions up to 4K

@60Hz (4:4:4)

COMPLIANCE WITH

HDMI STANDARD:

Supports HDR10, HDMI 2.0 and HDCP 2.2

INDICATOR LEDs: ON, IN, OUT 1 to 4

OPERATING

0° to +40°C (32° to 104°F)

TEMPERATURE:

STORAGE

 -40° to $+70^{\circ}$ C (-40° to 158° F)

TEMPERATURE:

HUMIDITY: 10% to 90%, RHL non-condensing

POWER

CONSUMPTION:

5V DC, 730mA

INCLUDED

ACCESSORIES:

Power supply

18.75cm x 11.50cm x 2.54cm (7.38" x 4.53" x 1.00") W, D, H

PRODUCT DIMENSION:

PRODUCT WEIGHT: 0.4kg (0.9lbs) approx

SHIPPING

34.50cm x 16.50cm x 5.20cm (13.58" x 6.50" x 2.05") W, D, H

DIMENSION:

SHIPPING WEIGHT: 1.0kg (2.1lbs) approx

