

Laser Distance Measurer, 50 m

MODEL NUMBER: T030-50M



Handheld laser distance meter with simple one-button operation measures up to 50 m (165 ft.) with +/-1 mm accuracy.

Features

Essential Tool for Cable Installers, Room Designers, Interior Decorators, Site Inspectors and Contractors

Easy One-Button Operation Makes Measuring a Cinch

Quickly Calculate Area and Volume

Modes for Measuring Unilateral Distances

LCD Screen Is Easy to Read Even at Night

Ready to Use Right Out of the Box

Highlights

- Simple one-button operation—just point and click for precise measurements
- +/-1 mm accuracy reduces estimation errors and saves you money and time
- Powers off automatically when not in use, improving AA battery life
- Backlit display for easy-to-read measurements at night or in dark places
- Included carrying case for convenient storage in toolbox or briefcase

Applications

- Measuring the distance between walls for electric wiring and interior decoration
- Installing digital signage where the displays are located far from the video source
- Determining the layout of a new factory floor
- Planning a new landscape for an atrium or outdoor garden

Package Includes

- T030-50M Laser Distance Measurer, 50 m
- Reflector board
- Hang rope
- (2) AAA batteries
- Carrying case
- Owner's manual

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>