

# 38WK95C-W

38" 21:9 IPS HDR WQHD+ USB Type-C Monitor

**38" 21:9 WQHD+ (3840x1600) IPS Display**

**HDR 10**

**sRGB 99%**

**USB Type-C**

**3-Side Borderless Design**

**Tilt / Height Adjustable Stand**



## PICTURE QUALITY

Screen Size	37.5"
Panel Type	IPS
Color Gamut (CIE1931)	sRGB 99% (Typ)
Color Depth(Number of Colors)	10bits (8bit+FRC), 1.07B
Pixel Pitch(mm)	0.229 mm x 0.229 mm
Response Time (GTG)	5ms (High)
Aspect Ratio	21:9
Resolution	3840 x 1600
Brightness	300(Typ), 240(min) cd/m <sup>2</sup>
Contrast Ratio	1000:1 (Typ)
Viewing Angle	178/178 (CR≥10)

## INPUT/OUTPUT

HDMI	Yes x 2
DisplayPort	Yes (ver1.2)
USB Type-C	Yes
Headphone Out	Yes
USB Down-stream	Yes (USB3.0 2ea)

## POWER

Type	Adapter
Input	100 ~240 , 50/60Hz
Output	60W
Normal On (factory out condition Typ.)	70W
Power Save/Sleep Mode (Max)	1.2W
DC Off (Max)	0.3W

## SPECIAL FEATURES

Picture Mode	(Non HDR Contents) --> Custom, HDR Effect, Reader:Photo, Cinema, Dark Room1/2, Color Weakness, FPS1 Game/FPS2 Game, RTS Game, Custom (Game), (HDR Contents) --> HDR Vivid, HDR Cinema , HDR Game, HDR Standard
Ratio	Wide, Original, Cinema 1, Cinema 2, 1 : 1
PIP	PIP mode in Screen Split
PBP	Yes
DDC/CI	Yes
HDCP	HDCP2.2 / HDCP1.4
Key Lock	Yes
Response Time Control	Yes
Adaptive Sync	AMD FreeSync™
Game Mode	Yes
DAS Mode	Yes
Black Stabilizer	Yes
Flicker Safe	Yes
Automatic Standby	Yes
Six Axis Control	Yes
Smart Energy Saving	Yes
Reader Mode	Yes
Super + Resolution	Yes
Color Calibrated	Yes
Dual controller	Yes
Screen split2.0 (in OSC)	Yes
On Screen Control (OSC)	Yes
Dual EDID (H/W)	Yes
One Click Stand Set-up	Yes
Super Resolution+	Yes
HDR (High Dynamic Range)	HDR 10

## SOUND

Speaker	Yes 10W x 2 (with Bluetooth)
Audio Tuning	Rich Bass

## DIMENSIONS/WEIGHT

With Stand (WxHxD)	35.3" x 19.5" (Down) x 9.3" 35.3" x 23.5" (Up) x 9.3"
Without Stand (WxHxD)	35.3" x 15.5" x 3.6"
Shipping Dimensions (WxHxD)	41.7" x 21.5" x 8.4"
With Stand Weight	19.8 lbs
Without Stand Weight	16.9 lbs
Shipping Weight	29.1 lbs

## STAND

Tilt(Angle)	-5~15 Degree
Height(mm)	100mm

## CABINET / ACCESSORIES

Wall Mount Size (mm)	100x100 (VESA compatible)
Power Cord	Yes
Display Port	Yes
HDMI	Yes
USB Type-C	Yes

## STANDARD

UL(cUL)	Yes
TUV-Type	Yes
FCC-B, CE	Yes
CCC (for China)	Yes
BSMI (for Taiwan)	Yes
ErP	Yes
Windows 10	Yes
DisplayPort	Yes

## LIMITED WARRANTY / UPC

Limited Warranty	1 Year Parts and Labor
UPC	719192617391
Country of Origin	China