

Lenovo Tablet 10 20L3000HUS

Region
US

Machine Type
20L3

TopSeller
TopSeller

Processor
Celeron N4100 (4C, 1.1 / 2.4GHz, 4MB)

Graphics
Integrated Intel UHD Graphics 600

Memory
4GB Soldered

Display
10.1" WUXGA (1920x1200) IPS

Multi-touch
10-point Multi-touch

Storage
128GB eMMC

Optical
None

WLAN + Bluetooth
11ac, 2x2 + BT4.1

WWAN
None

SIM Card
None

Camera
Front 2.0MP / Rear 5.0MP

Keyboard Docking
None

Pen
Lenovo Active Pen

Fingerprint Reader
Fingerprint Reader

NFC
None

TPM
dTPM 2.0

Battery
39Wh

Power Adapter
45W USB-C

Operating System
Windows 10 Pro 64

Warranty
1-year, Depot

Global
No

Ann Date (mm/yy)
04/18

Note:

Country Code "US" is for United States, "++" is for EMEA countries (e.g. AD - Saudi, Arabia, AT - Austria, BM - Bulgaria, etc.), "xx" is for EAST countries (e.g. BM - Bulgaria, CX - Hungary, CY - Cyprus, etc.), and "***" is for MEA countries (e.g. AD - Saudi, Arabia, ED - Egypt, EQ - Sweden, etc.). Please be aware that the EMEA/ EAST/MEA models listed above might not be available in all countries



This publication was developed for products and services offered in the United States and E.M.E.A countries. Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<http://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2018. All rights reserved.



Lenovo Tablet 10 Platform Specifications

Product Specifications Reference (PSREF)

Processor	Intel® Celeron Processor								Media reader Ports	None One USB 3.1 Type-A, one USB 3.1 Type-C Gen 1, one HDMI, headphone / microphone combo jack, one POGO keyboard connector, combo slot of nano-SIM card (WWAN models) and microSD card reader
	Processor Number	# of Cores	# of Threads	Clock Speed	Burst Frequency	Cache	Memory Types	Processor Graphics		
	N4000	2	2	1.1 GHz	2.6 GHz	4MB	LPDDR4-2133	Intel UHD Graphics		
N4100	4	4	1.1 GHz	2.4 GHz	Intel UHD Graphics					
Graphics	Intel UHD Graphics 600 in processor, supports 1080p video out via HDMI™ connector, HDCP-compliant								Camera	<i>Front camera:</i> 2.0-megapixel, fixed focus, flash LED <i>Rear camera:</i> 5.0-megapixel, auto focus
Chipset	Intel SoC (System on Chip) platform								Video capture	1080p video capture
Memory	<i>Some:</i> 4GB / 2133MHz LPDDR4 <i>Some:</i> 8GB / 2133MHz LPDDR4 <i>All:</i> no sockets, soldered to systemboard								Audio support	Realtek® ALC3240 codec / stereo speakers, 1.0 watt x 2 / 2 digital microphones, combo audio/microphone jack
Display	<i>Some:</i> 10.1" (256.5mm) HD (1280x800) , LED backlight, 300 nits, 16:10 aspect ratio, IPS <i>Some:</i> 10.1" (256.5mm) WUXGA (1920x1200) , LED backlight, 300 nits, 16:10 aspect ratio, IPS								Pogo Keyboard	<i>Optional:</i> Lenovo Tablet 10 travel keyboard
Multi-touch	OGS (One glass solution) Multi-touch screen, supports ten-finger gesture								Security	Kensington lock slot
Pen	<i>Optional:</i> Lenovo Active Pen for multi-touch display, on-board rechargeable								Security chip	Discrete TPM 2.0 TCG Certified
Storage	64GB or 128GB / eMMC (embedded Multi Media Card) flash memory on board								vPro & iAMT	None
Optical	None								Fingerprint reader	Touch style Fingerprint reader
Ethernet	None								NFC	<i>Optional:</i> Near Field Communication
Bluetooth™	Bluetooth 4.1 wireless, integrated in Wi-Fi + Bluetooth combo adapter								Battery - type	Lithium polymer, 39Whr
WLAN	RTL8822BE, 802.11ac, 2x2, WiFi + Bluetooth combo chip								Battery - life	up to 9.9 hr
WWAN	<i>Optional:</i> Integrated Mobile Broadband 4G LTE-A, Qualcomm® Snapdragon™ X7 LTE-A (Sierra Wireless EM7455)								AC adapter	45W or 65W USB Type-C AC adapter
SIM card (Micro)	<i>Optional:</i> Nano-SIM card slot, in the combo slot with microSD card reader								Light sensor	None
Smart Card Read	None								G-sensor	3D accelerometer
Dimensions	10.29" x 7.02" x 0.41"; 261mm x 178mm x 10.6mm								Compass	3D compass
Weight	<i>WiFi only:</i> from 1.46 lb (0.664kg); <i>WiFi + WWAN:</i> from 1.48 lb (0.672kg)								Gyroscope	3D gyrometer
Case color	Black								GPS	GPS function is integrated into WWAN module
Case material	PC and Glass Fiber Reinforced								Preload	<i>Some:</i> Windows 10 Pro 64 <i>Some:</i> Windows 10 Home 64
									Limited warranty	1-year - depot repair service/ service upgrades available
									Mil-Spec test	None
									Environment	RoHS, GREENGUARD, Low Halogen, US EPEAT GOLD



Lenovo Tablet 10

