


C9600

**OKI**  
PRINTING SOLUTIONS



The C9000 Series colour and mono printers

C9600n  
C9600dn  
C9600hdn  
C9600hdtm



 **C9000**  
Series



## Versatile printing at 36ppm colour & 40ppm mono. What more does your workgroup need?

Since we launched the award-winning C9000 Series in 2001, workgroups within all kinds of organisations have been empowered to enjoy the business benefits of fast, affordable colour and mono printing from a reliable, hardworking printer. But technology never stands still, and as businesses demand even more from their printers, it takes a business printing specialist like OKI Printing Solutions to deliver more.

So we now introduce the C9600 – an A4/A3 printer that sets new standards in high speed, high volume, high quality colour and mono printing. Delivering 36 pages per minute (ppm) colour and 40ppm mono A4, the C9600 is as fast a printer as you'll ever need. Reliability, flexibility, affordability, ease-of-use and professional quality results: the C9600 delivers all this and more. It is, quite simply, the best printer in its class for meeting the everyday demands of modern office life.

The C9600's superfast speed and steadfast reliability are due in no small part to OKI Printing Solutions' expertise in single-pass digital LED technology. Not only does the flat, straight paper path mean higher speeds, minimal jams and smoother handling of a wide range of paper types and formats, it also boasts a robust and impressive 150,000 pages per month duty cycle.




Project plan banners



Large volume mail outs

## The C9600 Colour and Mono Printers



### The C9600 features at a glance

	C9600n	C9600dn	C9600hdn	C9600hdtm
Colour speed (A4)	36ppm	36ppm	36ppm	36ppm
Mono speed (A4)	40ppm	40ppm	40ppm	40ppm
Resolution	ProQ2400	ProQ2400	ProQ2400	ProQ2400
Processor speed	720MHz	720MHz	720MHz	720MHz
Paper tray capacity (Standard)	530 + 230	530 + 230	530 + 230	2,120 + 230
Memory (Standard)	256MB	512MB	512MB	512MB
Auto Colour Balance	●	●	●	●
Duplex	○	●	●	●
Hard Disk Drive	○	○	●	●
High Capacity Feeder	○	○	○	●
Second tray	○	○	○	○
Saddle-stitch Finisher	○	○	○	○

● Standard ○ Optional

# Easy to use. Easy to create. Easier to make an impression.

Whatever you and your workgroup need to do the C9600 will help you do it fast, do it well and do it in-house. Need to print impressive-looking colour? The C9600 uses ProQ2400 Multilevel technology to produce results that exceed expectations, and Auto Colour Balance makes sure that those results remain consistent throughout the life of the printer. For advanced colour matching, you can also manage and store colour profiles on your printer's Hard Disk Drive (optional on C9600n/dn).



A3 spreadsheets



Saddle-stitched manuals

Need to produce a range of documents on various paper weights and sizes? Like business cards, CD labels or oversized A3 spreadsheets? Auto Media Detect optimises the printer to your required media type which increases efficiency. Need to print long project timing plans or posters? The C9600 offers banner printing up to 1.2m long. Need to produce saddle-stitched booklets or manuals? The C9600 offers full speed double-sided printing, and the optional Finisher will even fold, staple or hole-punch the results to give your documents that professional touch.

All the C9600's brilliant features would mean nothing if users were not able to put them to use quickly, easily and confidently. So at OKI Printing Solutions, we aim to empower everyone who uses our printers to produce exceptional results: first time, every time. We call this commitment **Chromability™ – in-house colour made easy, only from OKI Printing Solutions.**

You'll see evidence of this in our unique Template Manager software which allows you to quickly and easily create a range of striking documents. You'll see it in the free network utilities for print management and control. You'll see it in 'Ask OKI', a tab in your printer's driver which takes you to an information-packed web site specific to the C9600, to help you get the most out of your printer. And you'll see it in the C9600's informative graphical display panel which keeps every operation clear and simple for every user, every time.



(Optional Finisher pictured)

## Why OKI Printing Solutions?

We believe that effective printed communications are fundamental to successful businesses. That's why we focus purely on understanding their diverse printing requirements. Through our considerable technological resources we develop fast, high quality, cost-effective printing solutions that will benefit businesses today and long into the future.

It is the same progressive spirit that drove Kibitaro Oki to found Oki Electric in 1881, and which helped his company to become the global, multi-billion euro business that it is today. A business whose people share one single-minded purpose: helping other businesses grow and prosper by enabling them to create the best possible impression with their printed communications.

We led the way in making in-house colour printing fast and affordable. Now OKI Printing Solutions lead the way in making it easy. This means more than providing unique technologies and in-built functions like fast, single-pass colour, double-sided printing, and banner printing: it means making those functions as easy to use as possible – first time, every time. We call this **Chromability™ – in-house colour made easy, only from OKI Printing Solutions**. In short, it's about getting the most from your investment.

Our colour-coded segments are designed to help you save time. When you want to add another printing solution to your business, or check out the latest advances in technology on our website, simply use the colour guide below.

# High quality colour as fast as mono. Is your office up to speed yet?



MFPs



Colour Printers



Mono Printers



Fax



Dot Matrix Printers

# The C9600 Colour and Mono Printers

		C9600n	C9600dn	C9600hdn	C9600hdtm
Order number		01149001	01149101	01149201	01163901
Speed & throughput	A4 Print speed	36ppm colour, 40ppm mono			
	A4 OHP colour	10ppm colour, 16ppm mono			
	A3 Print speed	19ppm colour, 21ppm mono			
	Time to first print	10.5 seconds colour, 9 seconds mono			
	Warm up time	85 seconds or less from power on			
	Processor speed	720Mhz			
Print quality	Resolution	ProQ2400 Multilevel technology, 1200 x 600 dpi			
	Enhancements	Automatic Colour Balance ensures consistent colour at power on and at installation of new toner or drum; Auto Registration occurs on power up, when the cover is opened and after 400 printed pages (not in middle of printed job); Toner Save mode			
	Colour matching	Profile Assistant (C9600hdn, hdtm only), Oki Color Correct Utility, PS Gamma Adjuster			
Typefaces	Printer fonts	86 scalable PCL fonts, 1 bitmap font, 10 TrueType fonts, 136 Adobe® PostScript Type 1 fonts, OCR A/B, USPS Barcode			
Printing process		Single Pass Digital LED electrophotographic page printer with four image drum cartridges			
Compatibility	Printer languages	PCL5c, PCL XL (Colour), Adobe® PostScript 3 with direct PDF Printing (v1.3), SIDM			
	Connectivity	IEEE 1284 Bi-directional Parallel and Hi-speed USB 2.0, 10/100-TX Ethernet card, Wireless NIC-802.11g (Optional)			
	OS Compatibility	Windows 98 / 98 SE / ME / NT4 Workstation / NT4 Server (SP6 or later SP) / 2000 Workstation (SP3 or later SP) / 2000 Professional (SP3 or later SP) / 2000 Server (SP3 or later SP) / 2000 Advanced Server (SP3 or later SP) / XP Professional / XP Home / 2003 server / Mac OS 9.2, Mac OS 10.2.4 or later, Windows2000 Server (ServicePack4) + CitrixMetaFrameXP Presentation Server Feature Release3, Windows Server 2003 Standard Edition + CitrixMetaFrameXP Presentation Server Feature Release3			
	Network & protocols	10/100 Base TX Ethernet Card with internal Web Server for printer and network card set-up and management. Includes POP3/APOP and SMTP Mail client for submission of print jobs and for alerts. ALL major network protocols supported - TCP/IP, Netware and Ethertalk. TCP/IP :-ARP, RARP, IP, ICMP, TCP, UDP, LPR, FTP, TELNET, HTTP(IPP), BOOTP, DHCP, SNMP, DNS, SSL/TLS, JetDirect protocols. Netware 3.x, 4.x, 5.x and 6 with full NDS and NDPS support:- PServer, RPrinter, NDPS supported via dedicated OKI NDPS Gateway. EtherTalk:- ELAP, AARP, DDP, AEP, NBP, ZIP, RTMP, ATP, PAP. NetBEUI:- SMB, NetBIOS. Option Wireless LAN(802.11g)			
	Utilities	Print Control software allows ability to manage and control colour printing on the network; PrintSuperVision: Web-based software printer management tool; Oki Template Manager: easy-to-use software that enables simple creation of templates for printing business cards, banners and bar-coded documents; Storage Device Manager*: stores and manages forms, letterheads, logos and fonts. (*Hard Disk Drive required)			
Memory	RAM	256MB	512MB	512MB	512MB
	Max RAM	1024MB (Optional 128MB, 256MB, 512MB DIMMs)			
	Hard Disk Drive	Optional	Optional	Standard	Standard
	Paper handling	Internal tray 1: 530 sheets; Multi-purpose tray: 230 sheets; Optional 2nd/3rd paper tray: 530 sheets each; Maximum Paper Capacity (Printer + 2nd tray + High Capacity Feeder + Multi-purpose tray): 2,880 sheets			
	High Capacity Feeder	Optional (1,590 sheets)			Standard
	Paper weight	64–216gsm from internal tray (and optional trays), 55–268gsm from Multi-purpose tray, duplex 55–120gsm, sorter/mailbox (face up 64–268gsm, face down 64–216gsm)			
	Paper size	Internal and optional trays: 105mm–328mm width to 148mm–457.2mm length (including A6, A5, A4, A3, A3wide); Multi-purpose tray: 76.2mm– 328mm width to 127mm up to 1,200mm length (including A6, A5, A4, A3, A3wide and banner media)			
	Duplex	Optional	Standard		
	Paper feeding	Auto Media Detect: automatic paper weight detection; Auto Paper Tray Select: automatically detects paper size; Tray Empty Sensor; Tray Low Sensor			
	Paper output	Printer: 500 sheets face down, 250 sheets face up			
	Optional	Optional Finisher: stacks up to 1,000 sheets, up to 20 saddle-stitched booklets			
Operating conditions	Temperature/Humidity	10°C–32°C (17°C–27°C recommended) / 20% to 80% RH (50% to 70% RH recommended)			
	Storage	-20–45°C, 10–90%RH			
Power requirements	Power supply	Single phase 220–240VAC, frequency 50Hz +/- 2Hz			
	Power consumption	Typical 750W, Peak 1500W, Idle 200W (average), Power Save < 45W			
Noise level		Operating: 53dB(A) or less, Standby: 40dB(A) or less, Power save: 40dB(A) after 30 mins (background level)			
Dimensions (WxDxH)		654.5 x 620 x 461.5mm			654.5 x 620 x 785.5mm
Weight		72kg approx	77.4kg approx	77.4kg approx	129kg approx
Duty cycle	Printer duty (max)	150,000 pages/month			
Warranty		Pan European 1 year on-site			
Supplies life	Toner	15,000 pages @ 5% coverage per colour (printers are shipped with 7,500 pages worth of each toner @ 5% coverage)			
	Image Drum	30,000 pages @ average 3 pages/job			
	Waste Toner Box	30,000 pages average life			
	Fuser Unit	100,000 pages			
	Transfer Belt	100,000 pages @ average 3 pages/job			
Accessories		Internal Wireless Print Server (01163201); Duplex unit (C9600n only) (42797203); 2nd tray (42831303); High Capacity Feeder (standard on C9600hdtm) (42831503); 128MB RAM (01163401); 256MB RAM (01163402); 512MB RAM (01163403); C9600 HDD (C9600n, C9600dn only) (01163601); Finisher (4 tray)* (01166701); Finisher (5 tray)** (01166801); Finisher punch unit 2 hole (42872901); Finisher punch unit 4 hole (42872903); (* requires High Capacity Feeder; ** requires High Capacity Feeder & 2nd tray)			

**Consumables Information:** For the protection of your printer, and in order to ensure that you benefit from its full functionality, this model has been designed to operate only with genuine Oki toner cartridges. These can be identified by the Oki trademark. Any other toner cartridge may not operate at all, even if it is described as "compatible", and if it does work, your printer's performance and print quality may be degraded. Specification subject to change without notice. All trademarks acknowledged.

Description	Life* (pages)	Order Numbers
Toner Cartridge	15,000	Cyan: 42918915 Magenta: 42918914 Yellow: 42918913 Black: 42918916
Toner Rainbow pack	15,000	43112702
Image Drum	30,000	Cyan: 42918107 Magenta: 42918106 Yellow: 42918105 Black: 42918108
Transfer Belt	100,000	42931603
Fuser Unit	100,000	42931703
Waste Toner Box	30,000	42869403
Finisher staples	15,000	42937603

\* All toners: A4 pages @ 5%, Printer shipped with 7,500 pages @ 5%. All Drums: A4 pages average life

**OKI EUROPE LTD.**  
 Central House, Balfour Road  
 Hounslow, Middlesex TW3 1HY  
 United Kingdom  
 T +44(0) 20 8219 2190  
 F +44(0) 20 8219 2199  
[WWW.OKIPRINTINGSOLUTIONS.COM](http://WWW.OKIPRINTINGSOLUTIONS.COM)

Oki, Network Solutions  
 for a Global Society



As an ENERGY STAR Partner, Oki has determined that this product meets the ENERGY STAR guidelines for energy efficiency.

**OKI**  
 PRINTING SOLUTIONS