

GBU522

Bluetooth 4.0 Dual-Mode USB Mini Adapter



- Add Bluetooth connectivity to your desktop or laptop via a USB port
- Connects Bluetooth-compatible devices at distances of up to 49 ft. (15 meters)
- Dual-mode supports higher data rates, longer ranges and low power consumption
- Intelligently switches modes to support a wider variety of applications and devices
- Compatible with Bluetooth 4.0 Low Energy and Bluetooth 3.0 "classic"

Add Bluetooth Connectivity

The IOGEAR Bluetooth 4.0 Dual-Mode USB Mini Adapter adds connectivity to your desktop or laptop computer via its USB port. Connect to the latest Bluetooth-compatible devices like smartphones, tablets, wireless mice and keyboards, portable speakers and more from up to 49 feet away.

Dual-Mode Flexibility

The Dual-Mode Mini Adapter supports the latest Bluetooth 4.0 Low Energy technology and Bluetooth 3.0. Enjoy reduced power drain on notebook computers and other connected devices while supporting higher data rates and longer ranges with the same adapter.

- Add Bluetooth connectivity to your desktop or laptop via a USB port
- Connects Bluetooth-compatible devices at distances of up to 49 ft. (15 meters)
- Dual-mode supports higher data rates, longer ranges and low power consumption
- Intelligently switches modes to support a wider variety of applications and devices
- Compatible with Bluetooth 4.0 Low Energy and Bluetooth 3.0 "classic"
- Ultra-portable – Small enough to stay connected to your laptop when traveling
- LED indicator: Power on, Linking, Standby
- Bluetooth v4.0 certified by BQB (Bluetooth Qualification Body)





Requirements

- **Hardware Requirement:**
- Available USB-A port
-
- **Operating System:**
- For PCs: Windows® 8, Windows® 7, Windows Vista®, Windows XP®
- Windows® 10 is Plug and Play, requires no driver installation

Package Contents

- 1 x Bluetooth to USB adapter
- 1 x Driver Mini CD* (Windows® 10 requires no driver installation)
- 1 x Warranty Card

Warning: *The included CD is a mini size CD, and it is recommended not to insert and Play, requires no the mini size CD into the slot-loading CD ROM drive to avoid damaging the slot-loading CD ROM drive.

Specifications

| Function | GBU522 | Dimensions | GBU522 |
|-------------------------------|---|-------------------------|-----------------|
| Antenna Type | Printed on-board antenna | POP Information | |
| Frequency Band | 2.4GHz ~ 2.4835GHz ISM Band | 10" Peg Hook | 14 |
| Data Rate | maximum asynchronous transfer rate of 3Mbps | 6" Peg Hook | 8 |
| Interface | | Click Strip | 6 |
| Network Protocol | | Unit Dimensions | |
| Profiles Supported | Serial Port, Object Push, File Transfer, LAN Access, Personal Area Network, Audio Getaway, Heatset HID, Keyboard, Mouse, HCRP (Printer Cable Replacement), PIM Synchronization Profile, A2DP, AVRCP | Height | 0.7" (1.8 cm) |
| Operating Range | Up to 49ft (15m) | Depth | 0.51" (0.6 cm) |
| Operating Temperature | -10-50? | Length | 0.67" (1.7cm) |
| Operating System Requirements | | Inner Pack | |
| Windows | Windows XP®, Windows Vista®, Windows® 7, Windows® 8, Windows® 8.1 | Width | 4.33" (11cm) |
| | | Height | 6.30" (16cm) |
| | | Length | 5.12" (13cm) |
| | | Inner Pack Qty. | 12 |
| | | Unit Package Dimensions | |
| | | Width | 4" (10.2cm) |
| | | Height | 4.76" (12.1cm) |
| | | Depth | 0.39" (1cm) |
| | | Master Carton | |
| | | Width | 9.25" (23.5cm) |
| | | Height | 11" (28cm) |
| | | Depth | 6.69" (17cm) |
| | | Master Carton Qty. | 48 |
| | | Weight | |
| | | Master Carton Wt. | 3.09lb (1.4kg) |
| | | Inner Pack Wt. | 0.79lb (0.36kg) |
| | | Unit Pack Wt. | 0.05lb (0.02kg) |
| | | Unit Wt. | 0.01 lb |