



msi

GRAPHICS CARD GEFORCE® GT 1030 2GHD4 LP OC



SPECIFICATIONS

Model Name	GeForce® GT 1030 2GHD4 LP OC
Graphics Processing Unit	NVIDIA® GeForce® GT 1030
Interface	PCI Express 3.0 x16 (uses x4)
Core Name	GP 108-310
Cores	384 Units
Core Clocks	1189 MHz / 1430 MHz
Memory Clock Speed	2100 MHz
Memory	2GB DDR4
Memory Bus	64-bit
Output	DisplayPort / HDMI
HDCP Support	2.2
Power consumption	20 W
Recommended PSU	300 W
Card Dimension(mm)	150 x 69 x 38 mm
Weight (Card / Package)	304 g / 544 g
Afterburner OC	Y
DirectX Version Support	12
OpenGL Version Support	4.5
Maximum Displays	2
Accessories	Low Profile Bracket x 1

CONNECTIONS



FEATURES



COMPLETELY SILENT

Using an array of fins, this card uses passive cooling without any fans for absolute silence.



OC PERFORMANCE

MSI OC graphics cards are equipped with higher clock speeds out of the box for increased performance.



Military Class 4 Components

Using only the highest quality components means you get reliable and stable in-game performance.



LOW PROFILE DESIGN

Low Profile design saves space to allow building a slim/small form factor system.



PASCAL PERFORMANCE

Pascal-powered graphics cards give you superior performance and power efficiency to deliver the best gaming experiences.



MSI Afterburner

The ultimate overclocking software with advanced control options and real-time hardware monitor.