



## Display/image

Display technology	DLP
Resolution	1080p Full HD (1920x1080)
Brightness	4,000 lumens
Contrast ratio	100,000:1
ANSI contrast ratio	1,800
Contrast ratio - full on/off	100,000:1
Aspect ratio - compatible	4:3, 16:9, 16:10
Keystone correction - horizontal	30
Keystone correction - vertical	30
Uniformity	85%
Screen size	2.21m - 2.59m (87in - 102in)

## Lamp info

Light source	Laser
LASER life	20,000 hours

## Optical

Throw ratio	0.25:1
Projection distance (m)	0.46m - 0.55m
Zoom type	Fixed
Focal length (mm)	3.72mm
Lens shift	Vertical: +/-0%Horizontal: +/-0%
Native offset	120%

## Connectivity

Connections	<b>Inputs</b> 1 x VGA, 2 x HDMI, 1 x Audio 3.5mm, 1 x Mic 3.5mm, 1 x HDBaseT, 1 x RJ45 <b>Outputs</b> 1 x VGA, 1 x Audio 3.5mm <b>Control</b> 1 x RS232, 1 x mini USB service
-------------	---

## General

Noise level (typical)	32dB
PC compatibility	UXGA, SXGA, WXGA, HD, XGA, SVGA, VGA, Mac
2D compatibility	PAL (B, D, G, H, I, M, N, 576i/p), NTSC (M, 4.43/3.58 MHz, 480i/p), SECAM (B, D, G, K, K1, L) HD (1080i, 720p)
3D compatibility	Side-by-Side: 1080i50 / 60, 720p50 / 60 Frame-pack: 1080p24, 720p50 / 60 Over-Under: 1080p24, 720p50 / 60
3D	Full 3D
Security	Security bar, Kensington Lock
OSD / display languages	1 languages:
24/7 operation	Yes
Remote control	Wired backlit PRO AV remote
Speaker count	1
Watts per speaker	10W
In the box	HDMI Cable, IR Remote Control, AAA Batteries x2, Power Cord, Documentation

## Networking

LAN - control	Yes
LAN - DHCP	Yes

## Power

Power supply	AC 90 – 264V 50/60 Hz
Power consumption (standby)	0.5W
Power consumption (max)	335W

## Weight and dimensions

Net weight	5.5kg
Dimensions (W x D x H) (mm)	387 x 403 x 148

