

# IN119HDxa

InFocus

A Stunning Home Entertainment Experience

Part #: IN119HDxa

Whether you're screening a blockbuster, hosting a SuperBowl party, or facing off in a cutting-edge video game, everything comes to life in stunning HD with the high brightness and 3D capability of the IN119HDxa home projector.

## Key Features

- ◆ Full 1920 x 1080 HD resolution for exceptional image quality
- ◆ 3,600 lumens and high 28,000:1 contrast ratio make details pop
- ◆ Vivid and accurate color with BrilliantColor technology
- ◆ Display 3D content from Blu-ray, game consoles, and more



## 1080p HD resolution

Watch your favorite movies, sports, and games as they were meant to be seen, in full native 1080p resolution (16:9 aspect ratio). With no scaling or altering of the image, your picture will look better than ever and larger than life – at an affordable price.

## Advanced 3D Support

Powered by the latest DLP technology, the IN119HDxa displays stunning 3D content from PCs, Xbox, PlayStation, Blu-ray, and many other sources. Just add [144Hz DLP Link 3D glasses](#) (sold separately) to seamlessly synchronize with the image for an awesome 3D experience.

## HDMI CEC Compatible

The IN119HDxa is an HDMI Consumer Electronics Control (CEC) compatible device, so you can control it, and up to 14 other HDMI CEC compatible devices, with one remote.

## High Brightness and High Contrast

Meticulous attention to detail brings out amazing life-like details to create a fully immersive entertainment experience at home. 3,600 lumens give you images that come in bright and clear. 28,000:1 contrast ratio adds sharpness and depth with darker blacks and whiter whites.

## Specifications\*

Projector	IN119HDxa
Resolution – Native	Full HD (1920 x 1080)
Display Technology	DLP
Video Standard Compatibility	NTSC, PAL, SECAM, 480i, 480p, 576i, 576p, 720p, 1080i, 1080p

Projector	IN119HDxa
Speakers	Mono 10W x 1
Lamp Brightness	3,600 lumens
Lamp Brightness – Eco Mode	2,800 lumens
Lamp Life	5,000 hours
Lamp Life – Eco Mode	7,000 hours
Lamp Life – Dynamic Mode	15,000 hours
Lamp Power	195W
Lamp Power – Eco Mode	160W
Lamp Power – Dynamic Mode	83W
Replacement Lamp	SP-LAMP-100
Contrast Ratio	28,000:1
Number of Colors	1.07 billion
Synch Scan Frequency – Horizontal	15.375 - 91.146 KHz
Synch Scan Frequency – Vertical	24 - 85 KHz
Aspect Ratio	16:9
Aspect Ratio Compatibility	4:3, 16:10
Projection Distance – Minimum	2 m
Projection Distance – Maximum	10 m
Projection Lens F-Stop – Minimum	2.43
Projection Lens F-Stop – Maximum	2.78
Lens Type	Manual zoom and focus
Lens Shift – Vertical (max)	16%
Lens Shift – Horizontal (max)	N/A
Image Size – Minimum	42 in
Image Size – Maximum	300 in
Projection Offset	116% $\pm$ 5%
Keystone Correction	$\pm$ 40°
Connectors – Inputs	HDMI $\times$ 2, 3D Sync Out (5V), 3.5mm 12V Screen trigger, USB service
Connectors – Outputs	3.5mm audio output
Audible Noise	< dBA at 0°F / -17.8°C
Audible Noise – Eco Mode	< 24 dBA at 0°F / -17.8°C
Included Accessories	Power cord, Remote, VGA cable, Documentation
3D Support	DLP Link 3D glasses required
Product Warranty	2 years
Lamp Warranty	6 months
Accessories Warranty	90 days
Computer Compatibility	PC, Mac
Power Standard	AC 100 to 240V, 50/60
Operating Conditions	41 to 104°F at 0 to 10000 ft / 5 to 40°C at 0 to 3048 m
Menu Languages	English, French, German, Spanish, Italian, Norwegian, Dutch, Simplified Chinese, Traditional Chinese, Korean, Swedish, Russian, Finnish, Polish, Turkish, Danish, Arabic, Indonesian, Portuguese, Vietnamese, Czech, Romanian, Hungarian, Farsi, Japanese, Thai, Greek
Security Features	Kensington lock port, Security bar
Throw and Zoom	
Throw Ratio – Minimum	1.12:1
Throw Ratio – Maximum	1.47:1
Zoom Ratio	1.3:1
Shipping	
Product Dimensions	4 x 12.4 x 8.8 in / 101.6 x 315 x 223.5 mm
Product Weight	5.5 lbs / 2.5 kg
Shipping Dimensions	7.5 x 14.3 x 12 in / 190.5 x 362 x 304.8 mm
Shipping Weight	7.3 lbs / 3.3 kg

\* Product specifications, terms, and offerings are subject to change at any time without notice.

## Accessories

Universal Projector Ceiling Mount (PRJ-MNT-UNIV)  
Manual Pull Down Projector Screen: 106 in., 16:9 (SC-PDHD-106)  
Projector Lamp for the IN119HDxa (SP-LAMP-100)  
LiteShow 4 DB+ Dual Band Wireless Adapter (INLITESHOW4DB+)  
LiteShow Mount Adapter (PRJ-MNT-LS3)  
Soft Carry Case for Value Projectors (CA-SOFTVAL-2)  
Manual Pull Down Projector Screen: 92 in., 16:9 (SC-PDHD-92)  
Manual Pull Up Projector Screen: 73 in., 16:9 (SC-PUW-73)  
Manual Pull Up Projector Screen: 90 in., 16:9 (SC-PUW-90)  
DLP Link 3D Glasses by XPAND (X103-EDUX3-R1)  
1 Year Extended Warranty for IN1XX Projectors (EPW-PJV1)  
2 Year Extended Warranty for IN1XX Projectors (EPW-PJV2)