



- ▶ Exclusive ENERMAX LED LIGHTING Technology
- ▶ 3x ENERMAX T.B. RGB Fans Included
- ▶ Massive Cooling Potential with 4x Designated Places for Flexible Liquid Cooler Installation
- ▶ Defaulted Acrylic Front Panel and Additional Meshed Front Panel

SABERAY, a high-end RGB-sync gaming chassis, applies ENERMAX LED LIGHTING technology to deliver incredibly bright and even RGB lighting. The combination of RGB strips and 3x pre-installed ENERMAX T.B. RGB fans can offer up to 1280x RGB lighting effects. Furthermore, this RGB gaming castle supports 4x designated locations for liquid coolers or 9x locations for fans, giving enthusiasts and hardcore gamers great flexibility in liquid cooling configuration.



Features


▶ ENERMAX LED LIGHTING Technology

ENERMAX LED LIGHTING Technology + Innovative Nano Diffusant provide consistent and uniform luminance.



ENERMAX SABERAY

Incredibly bright and even lighting



Others

Uneven lighting with visible spots



- ▶ 3x pre-installed ENERMAX T.B. RGB fans with Patented Twister Bearing technology

With the patented Twister Bearing technology, the T.B. RGB fan provides beautiful lighting effects and offers superior silent performance.



■ Support RGB-sync with motherboards

Certified by ASRock, ASUS, GIGABYTE and MSI for RGB synchronization.



■ Amazing 1280x lighting effects

Saberay provides users with 5x modes and 256x colors to create the preferred lighting effects via the built-in controller.



■ Integrated control hub

For those who do not use the RGB-sync motherboards, the integrated control hub allows users to keep 5x RGB devices' lighting in sync; furthermore, the hub can also control the speed of the 6x fans together.



■ Unique quick-release design

The tool-less panels facilitate the system installation and maintenance.



Acrylic panel
(Default)



Meshed panel

► **Designed with both aesthetics and ventilation in mind**

Two premium tool-less front panels included.

- Glossy, full-view acrylic panel displays vivid lighting effects.
- Meshed panel provides better ventilation.



► **4mm panoramic tempered glass window**

The 4mm panoramic tempered glass window allows you to show off your rigs.

► **Anti-dust rubber plugs**



► **Solid structure with ample space**

Constructed of 0.8 mm sturdy steel, SABERAY offers spacious interior design for large, high-end components.






Extensive cooling potential


Flexible cooling system configuration supports 4x designated locations for liquid cooler installation.

Liquid Cooler Compatibility Chart					
Radiator size (mm)	360	280	240	140	120
Front	•		•		•
Top	•	•	•	•	•
Rear				•	•
Side			•		•



Flexible system configuration

Supports up to 1x 5.25" ODD, 2x 3.5" HDD, and 6x 2.5 SSD/HDD (2x Converted from 3.5" tray) to satisfy your storage needs.



■ **Support long VGA cards and tall CPU cooler**




■ **PSU-Tunnel design (aka PSU shroud)**

The design minimizes the cable clutter, which makes the system clean and neat, and helps improve the air circulation.

Dimensions

unit: mm



Specifications

Model Number			ECA3500BA-RGB
Dimensions			D478 x W223 x H566mm
Material			0.8mm SPCC
M/B Type			ATX, Micro ATX, Mini ITX
I/O		2x USB3.0, 2x USB2.0, HD Audio, Fan speed control, LED mode control, LED color control, Lumi switch	
Drive Bays	5.25"	1	
	3.5"	2	
	2.5"	6 (2x Converted from 3.5" trays)	
Expansion Slots			7
Fan Slots	Front	3x 120mm (3x 120mm T.B. RGB fans pre-installed)	
	Top	2x 140 or 3x 120mm	
	Rear	1x 140 or 1x 120mm (1x 140mm fan pre-installed)	
	Side	2x 120mm	
Liquid Cooling	Front	360 / 240mm radiator (62mm clearance)	
	Top	360 / 280 / 240mm radiator (63mm clearance)	
	Rear	140 / 120mm radiator	
	Side	240mm radiator	
PSU			Standard ATX Type
Clearance	Suggested VGA Card Length: 420mm (280mm with side radiator)		
	Suggested CPU Cooler Height: 175mm		
Shipping Information			
Barcode	EAN	4713157723437	
	UPC	819315023433	
Carton Dimensions			D625 x W318 x H573mm
Gross Weight			11.8kgs
Net Weight			10kgs

*Options vary by countries or regions.