



Monitor Rack-Mount Bracket, 4U, for LCD Monitor up to 17-19 in.

MODEL NUMBER: SRLCDMOUNT



Durable VESA bracket allows rack mounting of a flat-panel LCD monitor in a 19 in. floor rack enclosure or open frame rack.

Features

Easy Mounting of LCD Monitors or Televisions up to 19 in. This rack-mount monitor bracket is compliant with multiple VESA patterns, making it compatible with a wide range of retail LCD displays and touch-screen monitors up to 44 pounds. The SRLCDMOUNT supports LCD monitors up to 17 inches, which allows the display to fit snugly within a closed rack. If closing rack doors isn't an issue, simply reverse the rack-mount monitor bracket so that it's facing outward. With this configuration, the SRLCDMOUNT supports LCD monitors up to 19 inches. Compatible VESA mounting-hole patterns are 75 x 75 mm, 100 x 100 mm and 100 x 150 mm.

Includes Necessary Hardware for Mounting in 4U of Rack Space This VESA bracket fits all EIA-compliant 19-inch open frame racks and floor-standing rack enclosures. It's made from durable cold-rolled steel with a black powder-coated finish that blends seamlessly with your rack décor. Rack-mounting hardware is included, as well as a convenient Quick Start Guide that walks you through the simple rack-mounting process.

2-Year Warranty and Environmentally Responsible Design The SRLCDMOUNT comes with a 2-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

Highlights

- Fits 75 x 75, 100 x 100 and 100 x 150 VESA patterns to match wide variety of displays
- Compatible with all standard 19 in. open frame racks and floor rack enclosures
- Durable cold-rolled steel construction designed to stand up to heavy use over time
- Rack-mounting hardware included for immediate installation
- Supports LCD and touch-screen monitors up to 17-19 in. and 44 lb.

Applications

- Install an LCD display in an open frame or floor rack to monitor essential server-room or console information
- Mount a touch-screen display for instant on-site operation and control of rack equipment

System Requirements

- LCD display with 75 x 75 mm, 100 x 100 mm or 100 x 150 mm VESA plate

Package Includes

- LCD Mounting Plate
- (2) Rack Brackets
- (8) M6 x 16 Screws
- (8) M6 Cup Washers
- (8) M6 Cage Nuts
- (8) M5 x 10 Screws
- (8) M5 Flat Washers
- Installation Guide



Specifications

OVERVIEW	
UPC Code	037332213419
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
VESA Pattern (mm)	100x100; 100x150; 75x75
Maximum Weight Capacity (kg)	20
Maximum Weight Capacity (lbs.)	44
Rack Height	4U
Shipping Dimensions (hwd / cm)	20.32 x 48.77 x 52.83
Shipping Dimensions (hwd / in.)	8.00 x 19.20 x 20.80
Shipping Weight (kg)	7.08
Shipping Weight (lbs.)	15.60
Unit Dimensions (hwd / cm)	17.7 x 48.2 x 11.5
Unit Dimensions (hwd / in.)	6.97 x 18.98 x 4.53
Unit Weight (kg)	1.62
Unit Weight (lbs.)	3.57
Weight Capacity - Stationary (kg)	18
Weight Capacity - Stationary (lbs.)	40
STANDARDS & COMPLIANCE	
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>