

DocketPORT®

Convenience. Speed. Quality.™



Easily

Handles:



Documents



Receipts



Insurance Cards

DocketPORT.com is your official source for the entire DocketPORT line of products.

The next generation of personal productivity.

The DocketPORT 687 scans media at up to 600 dpi and its compact footprint fits in any office workstation. It can scan both sides of ID cards, driver's licenses, and embossed credit cards in one pass. This duplex scanner is USB powered so it will run off a desktop or laptop computer. Included software makes it easy to scan images into PDF, JPEG and TIFF file formats.

The DocketPORT 687 comes with a limited one year warranty and is durable and reliable for environments that demand high volume scanning.

DocketPORT 687

Duplex Card Scanner

Part Number: DP687

Features

Ultra compact footprint – Takes up far less space than comparable flat bed and ADF scanners; perfect for both portable and desktop users

USB power and convenience – No external power adapter required and "warm-up" wait time to scan

Professional grade quality – Durable and reliable for high-volume environments such as hospitals, banks, and points of sale

Scan directly to PDF – Included software conveniently delivers industry standard PDF output

Broad compatibility – Included TWAIN driver is compatible with thousands of software applications.

Includes DocketSCAN software – Easy to use, powerful imaging software

System Requirements

Pentium III 300 or Equivalent Processor
Windows 2000/XP/Vista
128 MB RAM (512 MB for XP and Vista)
200 MB hard disk
CD ROM Drive
USB Port

Specifications

Scan Modes	48-bit internal color, outputs 24-bit true color, 8-bit grayscale & 1-bit B&W
Scan Speed	6ppm B&W; 4ppm color (4" x 6" sheet) at 200dpi
Scan Area	Maximum 4.13" x 10" (101mm x 254mm)
Media Thickness	0.1 mm - 1.5mm
Interface	USB 2.0 (High Speed)
Optical Resolution	Up to 600dpi
Dimensions (LxWxH)	8" x 2.75" x 1.8" (203mm x 70mm x 46mm)
Scanner Weight	10.6oz (300g)
TWAIN and WIA compliant	Yes
Image Sensor	Dual, 2 linear color CMOS
Paper Sensor	Electro-Mechanical
Cable Length	60 inches (152 cm), detachable
Power Consumption	0.2W (standby), 2.0 W (during scan), fully USB powered
Regulatory Requirement	FCC Class B, CE, USB-IF.org
Environment Requirement	RoHS, WEEE
Part Number	DP687

DocketPORT® / www.docketport.com / 630-530-5400

DocketPORT 687/ **Part Number: DP687**

©2013 DocketPORT. All rights reserved. DocketPORT is a trademark. Features, specifications and bundled software application(s) and/or version numbers of software applications are subject to change without notice. Microsoft and Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. All trademarks and registered trademarks are the property of their respective owners.