

DocketPORT®

Convenience. Speed. Quality.™



Easily

Handles:

Documents

Receipts

Insurance Cards

DocketPORT.com is your official source for the entire DocketPORT line of products.

The next generation of personal productivity.

The DocketPORT 468 is the ideal simplex scanner for your needs. Its compact footprint and USB connectivity makes it convenient to use in the office or on the road. A versatile tool, the DocketPORT 468 scans all sizes of media from business cards all the way up to 8.5" x 14" documents. And with the ability to scan at up to 600dpi, you will always get crisp, clear results.

The scanner ships with a one year limited warranty and DocketSCAN II, an easy to use scanning program.

DocketPORT 468

Simplex Card & Document Scanner

Part Number: DP468

Features

Ultra compact footprint – Takes up far less space than comparable flat bed and ADF scanners; perfect for both portable and desktop users

USB power and convenience – No external power adapter required and no "warm-up" wait time to scan

Versatile scanning solution – Scans a wide variety of media from 2" x 3" business cards to 8.5" x 14" documents

Broad compatibility – Included TWAIN driver is compatible with thousands of software applications

High-resolution scanning – Scan any size document at 600dpi for crisp, clear results

Includes DocketSCAN II software – Powerful imaging software with a Scan-to-PDF utility

System Requirements

Pentium III 300 or Equivalent Processor
Windows 7 certified, Vista, XP, 2003, 2000
128 MB RAM (512 MB for XP and Vista)
200 MB hard disk
CD ROM Drive
USB Port

Specifications

Scan Modes	48-bit internal color, outputs 24-bit true color, 8-bit grayscale & 1-bit B&W
Scan Speed	5 ppm (pages per minute) B/W; 2 ppm Color
Scan Area	Maximum 8.5" x 14" (legal page)
Media Thickness	0.1 mm - 1.5 mm
Interface	USB 2.0 (High Speed)
Optical Resolution	600 x 1200 dpi
Dimensions (LxWxH)	11.5" x 2.0" x 1.7" (292 x 51 x 43mm)
Scanner Weight	12.0 oz (350g) without cable
TWAIN and WIA compliant	Yes
Image Sensor	CMOS CIS (Contact Image Sensor)
Paper Sensor	Mechanical
Cable Length	59 inches (150 cm)
Power Consumption	0.01W Suspend; 0.2W Stand by; 2.0W during scan
Regulatory Requirement	FCC Class B, CE,
Environment Requirement	RoHS, WEEE
Part Number	DP468

DocketPORT® / www.docketport.com / 630-530-5400

DocketPORT 468 / **Part Number: DP468**

©2013 DocketPORT. All rights reserved. DocketPORT is a trademark. Features, specifications and bundled software application(s) and/or version numbers of software applications are subject to change without notice. Microsoft and Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. All trademarks and registered trademarks are the property of their respective owners.