

# QCN8099B

## 5MP STARLIGHT BULLET CAMERA

### SPECIFICATIONS

<b>Camera Type</b> .....	Bullet Camera
<b>Camera Technology</b> .....	IP
<b>Image Sensor Size</b> .....	1/2.7"
<b>Image Sensor Type</b> .....	Progressive CMOS
<b>Megapixels</b> .....	5MP
<b>Effective Pixels</b> .....	2592 x 1944
<b>Lens Size</b> .....	2.8mm Fixed Lens
<b>Field of View</b> .....	H: 96°, V: 70°
<b>IR Cut Filter</b> .....	Yes
<b>Max. User Access</b> .....	1 Admin User w/ 9 Shared Users



### NIGHT VISION

Night Vision Range	Up to 98 ft
Infrared LED's	18

### IMAGE FEATURES

Video Compression	H.265+, H.265, H.264+, H.264
-------------------	------------------------------

### REMOTE MONITORING

Use as Standalone	Yes
Compatible Software	QC View, Q-See Plus
Compatible Mobile Devices	Android, iPhone, iPad
Compatible Systems	QC NVRs

### RESOLUTION & FRAME RATE

5MP (2592 x 1944)	20FPS
4MP (2560 x 1440)	20FPS
3MP (2304 x 1296)	25/30FPS
1080p (1920 x 1080)	25/30FPS
1280 x 1024 / 1280 x 920	25/30FPS
720p (1280 x 720)	25/30FPS

### POWER

Power Supply	DC 12V 0.5A 5W or PoE
Power Consumption	<4.85 W

### PTZ

Pan/Tilt	N/A
Digital Zoom	16x

### INTELLIGENT VIDEO ANALYSIS (IVA)

IVA Functions	Abandon, Intrusion, Missing Object, Tripwire
---------------	--

### AUDIO

Two-Way Talk	No
Audio Microphone	No
Speaker	No

### CONNECTIVITY

Connector Types	RJ-45 Ethernet
Wireless	No

### PHYSICAL ATTRIBUTES

Weatherproof	Yes
IP Rating	IP67
Body Construction	Metal + Plastic
Weight	0.97 lbs
Dimensions	2.76" x 6.49"
Operating Temperature	-22° to 140° F