

QCA8095B

4K ULTRA HD BULLET CAMERA

SPECIFICATIONS

Camera Type	Bullet Camera
Camera Technology	Analog HD
Image Sensor Size	1/2"
Image Sensor Type	CMOS
Megapixels	8MP
Effective Pixels	3840 x 2160
Lens Size	2.8mm Fixed Lens
Field of View	110° H
IR Cut Filter	Yes
Max. User Access	Depends on DVR



NIGHT VISION

Night Vision Range	Up to 66 ft
Infrared LED's	1

IMAGE FEATURES

Video Compression	H.264
-------------------	-------

REMOTE MONITORING

Use as Standalone	No
Compatible Software	Depends on DVR
Compatible Mobile Devices	Depends on DVR
Compatible Systems	QC PIR Analog Recorders

RESOLUTION & FRAME RATE

8MP/4K (3840 x 2160)	7FPS
6MP (3072 x 2048)	10FPS
4MP (2560 x 1440)	15FPS

POWER

Power Supply	DC 12V 0.7A
Power Consumption	6W (w/ LED On)

PASSIVE INFRARED

Detection Range	~33 ft. x 33 ft., 110°, 5 Zones
Pet Immunity	Up to 39 lbs

PTZ

Pan/Tilt	N/A
Digital Zoom	N/A

INTELLIGENT VIDEO ANALYSIS (IVA)

IVA Functions	No
---------------	----

AUDIO

Two-Way Talk	No
Audio Microphone	No
Speaker	No

CONNECTIVITY

Connector Types	BNC
Other Connections	No
Wireless	No

PHYSICAL ATTRIBUTES

Weatherproof	Yes
IP Rating	IP67
Body Construction	Plastic
Weight	10.6 oz
Dimensions	2.85" W x 3.27" H x 5.77" D
Operating Temperature	14° to 122° F