

QCN8096D

4K ULTRA HD DOME CAMERA

SPECIFICATIONS

Camera Type	Dome Camera
Camera Technology	IP
Image Sensor Size	1/2.5"
Image Sensor Type	Progressive CMOS
Megapixels	8MP
Effective Pixels	3840 x 2160
Lens Size	4mm Fixed Lens
Field of View	H: 87°, V: 48°
IR Cut Filter	Yes
Max. User Access	10 Users
Storage	Micro SD Card, Max. 128GB

NIGHT VISION

Night Vision Range	Up to 98 ft.
Infrared LED's	24

IMAGE FEATURES

Video Compression	H.265+, H.265, H.264+, H.264
-------------------	------------------------------

REMOTE MONITORING

Use as Standalone	Yes
Compatible Software	QC View, Q-See Plus (no Cloud)
Compatible Mobile Devices	Android, iPhone, iPad
Compatible Systems	QC NVRs

RESOLUTION & FRAME RATE

4K (3840 x 2160)	15FPS
3MP (2048 x 1536)	25FPS
1080p (1920 x 1080)	30FPS
720p (1280 x 720)	30FPS
D1 (704 x 576)	30FPS

POWER

Power Supply	DC 12V or PoE
Power Consumption	<5W



PTZ

Pan/Tilt	N/A
Digital Zoom	16x

INTELLIGENT VIDEO ANALYSIS (IVA)

IVA Functions	Tripwire, Intrusion, Abandon, Missing Object
---------------	--

AUDIO

Interface	1/1 Channel In/Out
Audio Microphone	No
Speaker	No

CONNECTIVITY

Connector Types	RJ-45 Ethernet (10/100Base-T)
Wireless	No

PHYSICAL ATTRIBUTES

Weatherproof	Yes
IP Rating	IP67
Body Construction	Metal
Weight	1.17 lbs
Dimensions	4.33" x 3.19"
Operating Temperature	-22° to 140° F