


Key Features

Discover the Amazing Details with Ultra HD Performance | Wide Range of Colours | AMD FreeSync™ Delivers Fluid, Tear-Free Visuals | HDR Delivers Stellar Contrast and Colour Accuracy | Picture-In-Picture (PIP)



Product Description

Whether for office use or for enjoying entertainment at home, VX3211-4K-mhd is designed to take your viewing experience to another level. VX3211-4K's Ultra HD resolution is 4X higher than Full HD, which maximizes efficiency and image detail due to increased coverage areas. VX3211-4K-mhd's wide colour gamut achieves 95% of NTSC colour size, meaning it can deliver more shades of viewable colours. AMD FreeSync™ virtually eliminates screen tearing and stuttering for a fluid gaming experience. A mega dynamic contrast ratio of 80M:1 gives images more depth and the user experience is enhanced in all facets of monitor usage. Built in Picture-in-Picture (PIP) mode lets you combine more content at the same time to increase efficiency. Moreover, HDR 10 can display specific levels of colour and brightness that exceed standard monitors, while built-in HDMI inputs and DisplayPort can support a wide range of devices to offer flexibility for your connection needs.



Visit Us = www.viewsonic.com

LCD PANEL		CONNECTOR		DIMENSIONS (W X H X D) (MM)	
Monitor Size:	32"W (31.5" Viewable)	Input:	HDMI x 2 (v2.0 compatible), DisplayPort x 1 (v1.2 compatible)	Physical with stand (mm):	729.7mm (W) x 495.5mm (H) x 230.31mm (D)
Panel Technology:	VA Technology, a-si TFT LCD	Output:	Earphone out x 1 (3.5mm plug)	Physical without stand (mm):	729.7mm (W) x 432.8mm (H) x 64.32mm (D)
Resolution:	Ultra HD 3840 x 2160	AUDIO		Packaging (mm):	838mm (W) x 615mm (H) x 282mm (D)
Display Area:	698.4mm (H) x 392.85mm (V)	Speaker:	2.5W x 2	WEIGHT	
Aspect Ratio:	16:9	POWER		Net with stand:	6.6kg (14.55lbs)
Brightness:	300 cd/m ² (Typ)	Power:	3-pin plug (CEE22) x 1	Net without stand:	5.75kg (12.68lbs)
Contrast Ratio:	3000:1 (Typ)	Voltage:	AC 100-240V (Universal); 50/60Hz	Gross:	10.06kg (22.18 lbs)
Dynamic Contrast Ratio:	80,000,000:1	Consumption:	50W	REGULATIONS	BSMI, RCM, GEMS, MEPS, PSE, VCCI, KC, e-Standby
Viewing Angles:	178 degrees / 178 degrees (Typ)	Optimize:	42W	WARRANTY	*Warranty offered may differ from market to market
Response Time:	GTG(AVR; Scaler OD) *2:3ms (Typ)	Conserve:	35W	PACKAGE CONTENTS	LCD Display Power Cable (1.5m) HDMI Cable (1.5m) Quick Start Guide
Backlight:	1 WLED light bar	ERGONOMICS			
Backlight Life:	30,000 Hrs (Min)	Tilt:	13 ~ -5 degrees		
Colours:	1.07 Billion colours (8-bit+Hi-FRC)	SPECIAL FEATURES			
Colour Gamut:	95% of NTSC colour size 86% NTSC colour coverage	Eye Care:	Blue light filter, Flicker Free		
Panel Surface:	Anti-Glare type, Hard-coating (3H), Haze 25%	WALL MOUNT			
INPUT SIGNAL		VESA@:	100mm x 100mm		
Frequency:	HDMI: Fh = 15 ~ 204KHz ; Fv = 40 ~ 60Hz DisplayPort: Fh = 135 ~ 135KHz ; Fv = 40 ~ 60Hz	OPERATING CONDITIONS			
Sync:	TMDS, PCI-E	Temperature (° F / ° C):	32°F to 104°F (0°C to 40°C)		
COMPATIBILITY		Humidity:	20% to 90% (no condensation)		
PC:	Windows 10 certified				
Mac@:	Power Mac tested				