

INF6533e

Customizable, open Android platform, 65-inch display

Part #: INF6533e

InFocus

With 4K resolution, Total Touch Control™, built-in education features, and the ability to natively run Android apps, the JTouch Plus INF6533e is a fully customizable, all-in-one teaching, collaboration, and presentation solution.

Key Features

- ◆ Navigate a friendly, easy-for-anyone interface with Total Touch Control
 - no need for a remote
- ◆ Built-in whiteboard, browser, file explorer, as well as AirPlay and EShare for wireless casting
- ◆ Annotate over any application or video input
- ◆ Comment and draw over websites, documents, and more
- ◆ Brilliant 65-inch, 4K resolution screen with anti-glare
- ◆ Add any Android app
- ◆ Customize your whiteboard background



Open Android Platform

Expand and customize your platform with any Android application or game. Simply download and install as you would on your phone.

Four Critical Applications

All JTouch Plus models include the four critical applications needed for interactive touch panels: Casting, Whiteboarding, Browsing, and File Viewing. Create on a full-featured digital whiteboard, present videos and photos, browse the web, easily connect and share content from your Apple, Windows, or Android devices with wireless casting.

Intuitive Touch

Erase, zoom, and pull up menu options quickly and easily with incredibly intuitive touch gestures on the JTouch Plus. Use one finger to draw, two fingers to move, and three fingers to erase on the whiteboard or when annotating on any screen. A simple

swipe gesture on either side of the screen reveals a full menu of further options.

Interactive Whiteboard

Draw, write, and capture notes on a fully customizable, built-in digital whiteboard. Choose any background on a multi-screen canvas with room for free-form drawings, diagrams, and more. Draw using your finger or one of the provided styli using a complete collection of digital pens, highlighters, shapes, lines, and colors.

Multi-input Touch Monitor

Plug up to eight devices into your INF6533e monitor. HDMI-based sources can also connect via five separate USB-B ports to access the panel's touch control. Front access IO ports make it convenient to connect, view, and touch control any user's PC temporarily with both HDMI and Touch USB.

Optional PC

Turn your INF6533e into a fully integrated, powerful all-in-one Windows 10 PC with touch by adding the optional Core i5 OPS PC Module (coming soon).

Specifications*

Display		INF6533e
Diagonal Size		65"
Resolution – Native		4K UHD (3840 x 2160)
Display Technology		Direct-LED backlight
Touch Screen Features		Multi-touch, Anti-glare, Anti-Fingerprint
Glass Strength		4mm thick, heat treated
Scratch Resistance		7 Mohs
Contrast Ratio		1,200:1
Display Brightness		450 cd/m2
Refresh Rate		120 Hz
Response Time		8.0 ms
Pixel Pitch		0.429 mm
Viewing Angle		176°
Speakers		Stereo 10W x 2
Display Connectors – Inputs		RS232, Component video, Composite video, HDMI x 5, RJ-45 (Ethernet), VGA, USB 3.0 x2, Media USB (Android), PC Audio In (stereo, VGA Audio source), 1/8" Microphone (Mono linked to OPS), USB 2.0 x2, OPS PC USB x2, RCA L/R audio
Display Connectors – Outputs		3.5mm stereo audio, RS232, HDMI, SPDIF, 3.5mm Headphone, RCA L/R audio, USB-B x5 for Touchscreen Control
Power Standard		AC 100 to 240V, 50/60
PC		
PC Hardware		OPS Bay
System		
Included Accessories		Power cord, Remote, Stylus, HDMI Cable, USB cable, Quick Start Guide, USB WiFi Adapter
Wireless Collaboration		Casting embedded
Audible Noise		< 40 dBA at 77°F / 25°C
Operating Conditions		32 to 104°F at 0 to 10000 ft / 0 to 40°C at 0 to 3048 m
Power Consumption		207.0W max
Mounting Pattern		VESA 400×600mm with M8 screws
Product Warranty		2 years
Product Dimensions		35 x 59.5 x 4.8 in / 889 x 1511.3 x 121.9 mm
Product Weight		117 lbs / 53.1 kg
Shipping Dimensions		45.9 x 69.5 x 12.6 in / 1165.9 x 1765.3 x 320 mm
Shipping Weight		147 lbs / 66.7 kg

* Product specifications, terms, and offerings are subject to change at any time without notice.

Accessories

1 Year Extended Warranty for 65-inch JTouch (EPW-65JT1)
Mobile Cart for up to 75-inch Displays (INF-MOBCART)
SimpleShare Presentation System (INA-SIMPS1)
SimpleShare Touch Presentation System (INA-SIMINT1)
SimpleShare (INA-SIMS1)
LiteShow 4 DB+ Dual Band Wireless Adapter (INLITESHOW4DB+)
Remote Control for Mondopad, BigTouch or JTouch (INA-REMOTE2)
Mini USB WiFi Adapter (INA-WIFIUSB-3)

Wall Mount for up to 75-inch Display (INF-WALLMNT2)
Lift Case for 55-inch to 65-inch Displays (CA-ATALIFT65)
Mobile Cart Pro for up to 75-inch Displays (Black) (INF-MOBCARTPRO-B)
Mobile Cart for Vertical Lift Mount (INA-CARTBB)
VESA Interface Bracket for Vertical Lift Mounts (INA-VESABB)
Vertical Lift Display Wall Mount (INA-MNTBB70)
Floor Support for Lift Wall Mount (INA-SUPPORTBB)
2 Year Extended Warranty for 65-inch JTouch (EPW-65JT2)
3 Year Extended Warranty for 65-inch JTouch (EPW-65JT3)