

OVERVIEW

Basic rPDUs deliver reliable power to critical IT equipment within a rack or cabinet.

Benefits

- Reliable rack power distribution.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.
- Standard three-year warranty, upgraded to a five-year warranty with product registration.



Part #: VP9563

Model Number: BRN100-1025

Category: Basic

Sub Category: Standard

Power Configuration: 20A, 120V, 1.9kW

Physical Configuration: 19in / 483mm, Horizontal

Product Summary: VP9563 - rPDU, Basic Standard, 20A, 120V, 1.9kW, Horizontal, (10) NEMA 5-20R, 10ft power cord with 5-20P, Black Powder Coat.

Plug Form:



5-20P

Receptacle:



NEMA 5-20R
(Quantity: 10)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

| | |
|------------------------------|---------|
| Quantity Of Inputs | 1 |
| Voltage | 120V |
| Current | 20A |
| VA per Input (Load Capacity) | 1.9kW |
| Frequency | 50/60Hz |

| | |
|---|---|
| Over Current Protection | 20A Thermal Breaker |
| Switch | No |
| Indicators - LED(s) | 1 - Power ON Green LED |
| Power Cable Wire Gauge | 12/3 |
| Power Cable Length | 10ft |
| Plug Type | NEMA 5-20P |
| Receptacle/Socket Type #1 | NEMA 5-20R |
| - Quantity on Rear | 10 |
| - Quantity per Breaker | 10 |
| - Style | Duplex |
| - Maximum Output per Receptacle/Socket | 20A |
| - Voltage per Receptacle/Socket | 120V |
| Continuous Operating Temperature Range | 10-45C / 50-113F |
| Heavy Steel - Powder Coat Finish | Black |
| Configuration | 19in / 483mm Horizontal Rackmount |
| Flush Mount | Yes |
| Made in the USA | Yes, TAA Compliant |
| Product Warranty | 5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years |
| Certification/Agency Approvals | RoHS Compliant |
| Certification/Agency Approvals | UL & c-UL Listed 60950 |
| Chassis Dimensions (HxWxD) | 1.72in x 17in x 3.75in |
| Shipped Weight | 6lbs (2.72kg) |