

## SmartRack Sound Proof Server Rack - Quiet Acoustic Server Rack, 18U

MODEL NUMBER: SRQ18U



Quiet server rack secures and organizes standard rack equipment in IT networking areas where sound needs to be reduced.

### Features

**Quiet Server Rack Muffles Loud Network Equipment for a Less-Stress Work Environment** This acoustic server rack is specifically designed to minimize external acoustic levels caused by network equipment. The SRQ18U is ideal for small offices, recording studios, retail applications, classrooms and other areas where you need equipment to be secure, organized and quiet. Special foam sound-dampening baffles are built into the front and rear doors and side panels to reduce acoustic levels by as much as 28 decibels. Less noise makes for a calmer work environment that encourages productivity.

**Secures and Organizes Rack Equipment in 18U of Space** This quiet rack enclosure accommodates all EIA-standard 19-inch rack-mount equipment up to 45 inches deep. It has a maximum stationary load capacity of 750 lbs (340.2 kgs) and a rolling load capacity of 750 lbs (340.2 kgs). It's constructed from heavy-duty steel with a durable black powder-coated finish and a professional MDF overlay that fits into the room décor just like a regular piece of furniture.

**Unique Airflow Design Cools Equipment for Maximum Performance** A unique airflow design maximizes cooling by drawing in cool air through the bottom panel intake, passing it horizontally through the enclosure, and using ten built-in electric fans to push warm air out through the side panels. Two vertically mounted fan banks plug into a six-outlet 15A power strip, which leaves four outlets open for connecting equipment or accessories. The power strip connects to a standard 120V AC outlet.

**Protects Your Valuable Equipment against Vandals and Thieves** The split front and rear doors lock securely to help prevent damage, tampering or theft. A convenient cable brush strip on the bottom panel allows easy cable routing through the quiet rack enclosure while keeping dust and debris out.

**Ships Fully Assembled for Immediate Deployment and Equipment Installation** The 18U acoustic rack cabinet comes fully assembled and ready to deploy with pre-installed casters that let you easily maneuver it through standard doorways into proper position, where it can be secured using the included shipping bracket. Square mounting holes and numbered rack spaces make equipment installation easy. The vertical mounting rails adjust in 3/8-inch increments to accommodate equipment up to 45 inches deep.

**Meets Payment Card Industry Standards** The SRQ18U provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance.

**5-Year Warranty** The SRQ18U is backed by a 5-year warranty, ensuring reliability and performance.

### Highlights

- Secures 18U of EIA-standard 19 in. rack equipment up to 37 in. deep
- Minimizes equipment noise by as much as 28 decibels for quieter work environment
- Floor panel intakes and built-in fans keep equipment cool to maintain top performance
- Steel/MDF cabinet locks securely to help prevent equipment damage or theft
- Ships fully assembled for immediate deployment and equipment mounting

### Applications

- Store and organize 19 in. rack equipment in areas where quiet is essential, such as small offices, recording studios, retail locations and classrooms
- Deploy in a back room or network closet in an office too small to accommodate a server room or data center

### Package Includes

- SRQ18U SmartRack Sound Proof Server Rack - Quiet Acoustic Server Rack, 18U
- Rack-mounting hardware
- (2) Keys
- Owner's manual

## Specifications



<b>OVERVIEW</b>	
UPC Code	037332212979
Device Compatibility	Patch Panel; Network Switch; UPS; Server
Rack Type	Enclosure
<b>PHYSICAL</b>	
Color	Beige; Black
Factory Preset Rack Depth (in.)	29
Factory Preset Rack Depth (cm)	73.7
Factory Preset Rack Depth (mm)	737
Maximum Device Depth (cm)	93.98
Maximum Device Depth (in.)	37
Maximum Device Depth (mm)	940
Minimum Device Depth (cm)	40.64
Minimum Device Depth (in.)	16
Minimum Device Depth (mm)	406
Rack Height	18U
Shipping Dimensions (hwd / cm)	111.20 x 81.20 x 123.70
Shipping Dimensions (hwd / in.)	43.78 x 31.97 x 48.70
Shipping Weight (kg)	122.92
Shipping Weight (lbs.)	271.00
Unit Dimensions (hwd / cm)	97.8 x 76.2 x 118.6
Unit Dimensions (hwd / in.)	38.6 x 30.0 x 46.7
Unit Weight (kg)	109.77
Unit Weight (lbs.)	242.00
Weight Capacity - Rolling (kg)	340
Weight Capacity - Rolling (lbs.)	750
Weight Capacity - Stationary (kg)	340
Weight Capacity - Stationary (lbs.)	750
Rack Depth	Standard
Number of Vertical Mounting Rails	4
<b>SPECIAL FEATURES</b>	
Grounding Lug	Front and back floor panel
Built-in Cable Management	Yes



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	RoHS; IP20 Protection Rating
Approvals	EIA/ECA-310-E
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>