

QCN8093B

4K ULTRA HD COLOR NIGHT VISION BULLET CAMERA

SPECIFICATIONS

Camera Type	Bullet Camera
Camera Technology	IP
Image Sensor Size	1/2"
Image Sensor Type	Progressive CMOS
Megapixels	8MP
Effective Pixels	3840 x 2160
Lens Size	2.8mm Fixed Lens
Field of View	H: 131°, V: 111°
IR Cut Filter	Yes
Max. User Access	20 Users



NIGHT VISION

Night Vision Range	160 ft
Infrared LED's	2

IMAGE FEATURES

Video Compression	H.265+, H.265, H.264+, H.264
-------------------	------------------------------

REMOTE MONITORING

Use as Standalone	Yes
Compatible Software	QC View
Compatible Mobile Devices	Android, iPhone, iPad
Compatible Systems	QC NVRs

RESOLUTION & FRAME RATE

8MP (3840 x 2160)	Up to 30FPS
6MP (3072 x 2048)	Up to 30FPS
5MP (2560 x 1920)	Up to 30FPS
3MP (2048 x 1536)	Up to 30FPS
3MP (2304 x 1296)	Up to 30FPS
1080p (1920 x 1080)	Up to 30FPS
1.3MP (1280 x 960)	Up to 30FPS
720p (1280 x 720)	Up to 30FPS

POWER

Power Supply	DC 12V 1A or PoE
Power Consumption	<7.8 W

PTZ

Pan/Tilt	N/A
Digital Zoom	16x

INTELLIGENT VIDEO ANALYSIS (IVA)

IVA Functions	Abandon, Intrusion, Missing Object, Tripwire
---------------	--

AUDIO

Two-Way Talk	No
Audio Microphone	No
Speaker	No

CONNECTIVITY

Connector Types	RJ-45 Ethernet 10/100 Mbps
Wireless	No

PHYSICAL ATTRIBUTES

Weatherproof	Yes
IP Rating	IP67
Body Construction	Metal + Plastic
Weight	1.17 lbs
Dimensions	2.76" x 7.09" x 2.76"
Operating Temperature	-22° to 140° F