

P300 NEO

PICO PROJECTOR



TINY | BRIGHT | MOBILE

1280X720 HD NATIVE RESOLUTION

420 LUMENS | 30K HOUR LEDS | 2.5 HOUR BATTERY

HD Entertainment Anytime, Anywhere

Incorporating the latest in LED technology along with a 1280x720p imager, the P300 Neo produces a vivid high definition picture anytime, anywhere. Powered by a 30,000 hour LED light source and a 150 minute lithium ion battery, the P300 Neo can deliver up to 120" images in dark areas* with 420 lumens and offers best-in-class resolution for both its size and price.



Photos



Music



Text



Videos



Onboard Media Player



30,000 Hour LED



150 Minute Battery



120" Screen Size



Digital Keystone

www.aaxatech.com

aaxa
TECHNOLOGIES

PROJECTION SYSTEM

Max Resolution: 1920x1080 (1080p)
Native Resolution: 1280x720 (720p)
Max Brightness (DC): 420 Lumens
Contrast Ratio: 1000:1
Projection Lens: Manual Focus
Projection Image Size: 10"-120"
Lamp: Triple RGB LEDs with Vibrant Color Technology - Life 30,000hrs

GENERAL SPECIFICATIONS

Battery Runtime: 150 Minutes (Eco Mode)
Audio Output: 1W Speaker
3.5mm Headphone Output
Color: Black / White
File Playback: MicroSD & USB Host reader
Menu Language: English, Spanish, French, Chinese (Traditional/Simplified), Dutch, Korean, & Japanese
Aspect Ratio Control: 16:9
Dimensions: 5.9" x 3.5" x 1.2"
Weight: 0.84 LBS
Power Consumption: 24 Watts
Supported Formats: MP3 / WMA / OGG / WAV / AVI / BMP / JPG / GIF / TXT
Conformances: CE, FCC Class A



INPUTS / OUTPUTS

Video In: HDMI, Composite A/V (3.5mm Jack), mini-VGA
Audio Out: 3.5mm Stereo Headphone Jack
USB: Full Sized USB 2.0

ONBOARD MEDIA PLAYER

Processor: ARM Cortex 1.3 ghz
Operating System: Linux Based

THROW RATIO

Throw Ratio: 1.2
Projection Offset: 100%

INCLUDED ACCESSORIES

- ✓ User Manual
- ✓ Tripod
- ✓ Composite AV Cable
- ✓ Wall Charger
- ✓ Remote Control




Digital Video Input



TF Card/USB



VGA Input



Composite A/V



3.5mm Audio Jack



P300 NEO
PICO PROJECTOR

www.aaxatech.com

aaxa
TECHNOLOGIES