

# HP LD4312 4K Large Format Display



Inspire collaboration and productivity among small huddle groups with the HP LD4312 4K UHD Display. See and hear every detail in 3840 x 2160 resolution on a 43" diagonal screen with integrated dual stereo speakers.



## Show and share everything

- Experience excellent content readability and brilliant imagery from more than 8 million pixels and 3840 x 2160 resolution. Get great views from anywhere in the room with 178-degree wide viewing angles.

## Ready to collaborate

- Pair the display with an HP Elite Slice for Meeting Rooms, HP Collaboration PC with Intel Unite® software or HP Chromebox to turn your everyday conference room into a world-class collaboration center.<sup>1</sup>

## Set up in moments

- Quickly connect to your video source with DisplayPort™ 1.2, HDMI 1.4, HDMI 2.0 or VGA. Enjoy stereo audio from two integrated 6W speakers and control settings with the included remote.

## Featuring

- Use the display in huddle rooms and workspaces where you need large-scale views of data and content, or mount on a wall in small spaces with the integrated VESA mount.
- Rest assured that your IT investment is supported by a three-year standard limited warranty. To extend your protection, select an optional HP Care service.

## HP LD4312 4K Large Format Display Specifications Table



<b>Display Type</b>	ADS with LED backlight
<b>Panel Active Area</b>	94.11 x 52.94 cm
<b>Display Size (diagonal)</b>	109.22 cm (43")
<b>Viewing Angle</b>	178° horizontal; 178° vertical
<b>Brightness</b>	250 cd/m <sup>2</sup> <sup>1</sup>
<b>Contrast Ratio</b>	1200:1 static; 8000000:1 dynamic <sup>1</sup>
<b>Response Ratio</b>	8 ms gray to gray <sup>1</sup>
<b>Product colour</b>	Sky gray
<b>Aspect Ratio</b>	16:9
<b>Native Resolution</b>	4K UHD (3840 x 2160 @ 60 Hz)
<b>Resolutions Supported</b>	1024 x 768; 1280 x 1024; 1440 x 900; 1600 x 900; 1920 x 1080; 1920 x 1200; 2560 x 1440; 2560 x 1600; 3840 x 2160; 640 x 480; 720 x 400; 800 x 600
<b>Display Features</b>	Anti-glare; Language selection; LED backlights; On-screen controls; Plug and Play; User programmable
<b>User Controls</b>	Audio control; Brightness; Color control; Image control; Information; Management; PIP control; Power control; Input control; Menu control
<b>Input Signal</b>	1 DisplayPort™ 1.2; 1 HDMI 1.4; 1 VGA; 1 HDMI 2.0 (with HDCP support for HDMI and DisplayPort™)
<b>Ports and Connectors</b>	1 audio (in/out); 1 USB 2.0
<b>Input Power</b>	Input voltage 100 to 240 VAC
<b>Power Consumption</b>	100 W (maximum), 82 W (typical), 0.5 W (standby)
<b>Weight</b>	7.4 kg Head only.
<b>Physical security features</b>	Security lock-ready <sup>2</sup>
<b>Multimedia</b>	Dual 6 W speakers
<b>Environmental</b>	Operating temperature: 0 to 40°C Operating humidity: 20 to 80% non-condensing
<b>Energy Efficiency Compliance</b>	ENERGY STAR® certified; EPEAT® Silver
<b>Certification and compliance</b>	Bauart; BIS; BSMI; CB; CCC; CE; CECP; CEL Grade 2; C-Tick; cTUVus; EAC; ErP; E-standby; FCC; ICES; KC; Mexico CoC; MSIP; PSB; REACH; SABS IEC 60950-1; SASO; SEPA; S-Mark; SmartWay Transport Partnership (NA); TUV-S; VCCI; WEEE; ISC; MPRI; GOST-R; SII; EU RoHS; Voluntary materials restrictions
<b>Environmental Specifications</b>	Mercury-free display backlights
<b>What's in the box</b>	AC power cord; DisplayPort™ 1.2 cable; Documentation; HDMI cable; Warranty card; Remote controller

See important legal disclaimers on the last page

## Recommended Accessories and Services

### HP 5-year Next Business Day

XLarge Monitor Only  
Hardware Support



Receive 5 years of next business day onsite repair from an HP-qualified technician for your computing device, if the issue cannot be solved remotely. For more information on Care Pack services, please visit [www.hp.com/go/cpc](http://www.hp.com/go/cpc).

**Product number: UE370E**

## Messaging Footnotes

<sup>1</sup> PC products sold separately.

<sup>2</sup> Stand and wall mounting hardware sold separately.

<sup>3</sup> HP Care Packs sold separately. Service levels and response times for HP Care Packs may vary depending on your geographic location. Service starts on date of hardware purchase. Restrictions and limitations apply. For details, visit [www.hp.com/go/cpc](http://www.hp.com/go/cpc). HP Services are governed by the applicable HP terms and conditions of service provided or indicated to Customer at the time of purchase. Customer may have additional statutory rights according to applicable local laws, and such rights are not in any way affected by the HP terms and conditions of service or the HP Limited Warranty provided with your HP Product.

## Technical Specifications Footnotes

<sup>1</sup> All specifications represent the typical specifications provided by HP's component manufacturers, actual performance may vary either higher or lower.

<sup>2</sup> Lock is sold separately.

## Sign up for updates

[hp.com/go/getupdated](http://hp.com/go/getupdated)

© Copyright 2018 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein. EPEAT® registered where applicable. EPEAT® registration varies by country. See [www.epeat.net](http://www.epeat.net) for registration status by country. See HP's 3rd party option store for solar energy accessory at [www.hp.com/go/options](http://www.hp.com/go/options)

ENERGY STAR® and the ENERGY STAR® mark are registered trademarks of the U.S. Environmental Protection Agency. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. USB Type-C™ is a trademark of USB Implementers Forum.

