

Cat5e 350 MHz Molded Shielded (STP) Ethernet Cable (RJ45 M/M) - Gray, 7 ft. (2.13 m)

MODEL NUMBER: N105-007-GY



Highlights

- Protect your network data from EMI/RFI interference
- Molded boot provides extra strain-relief and durability

Package Includes

- 7-ft. (2.13 m) Gray Cat5e Shielded STP Patch Cable

Description

Protect your high-speed network from noise and electromagnetic interference with Tripp Lite's 7-ft. (2.13 m) gray, Category 5e (Cat5e) Shielded patch cable. This STP cable features 2 shielded RJ45 gold molded male connectors with integral strain relief. The cable is manufactured from PVC, 4-pair, stranded shielded twisted pair, and is rated for 350MHz/1Gbps communication.

Features

- Provides EMI/RFI shielding in Ethernet networks
- Shielded RJ45 connectors with gold-plated contacts
- 4-pair 24 AWG Stranded STP with drain wire
- Molded boot for extra strain-relief and durability
- TSB 568B (AT&T 258A)Wiring
- TIA/EIA and UL Certified

Specifications

OVERVIEW	
UPC Code	037332124326
Technology	Cat5/5e
PHYSICAL	
Color	Gray
Cable Shielding	FTP



Cable Jacket Material	PVC
Cable Jacket Rating	CM
Number of Conductors	4 Pair
Conductor Material	Stranded Copper
Conductor Gauge	24 AWG
Cable Length (ft.)	7
Cable Length (m)	2.1
Cable Length (in.)	84
Cable Length (cm)	213.4
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.10
Shipping Weight (lbs.)	0.23
COMMUNICATIONS	
Bandwidth per TIA Standard	100 MHz
Maximum Bandwidth as Tested	350 MHz
Maximum Data Rate	1Gbps
Network Speed	1Gbps
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Connector Type	Molded
Wiring Configuration	EIA/TIA 568B
FEATURES & SPECIFICATIONS	
Cable Style	Shielded; Molded
SPECIAL FEATURES	
IP68 Rated	No
Snagless Connector	No
Antibacterial	No
STANDARDS & COMPLIANCE	
Certifications	RoHS-Compliant



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>