

7" USB Vesa 75 Multi-Point Captive Touch Display

UM-760C-SMK



USB-driven LCD monitors are a friendly and affordable way to add a display to any computer or interface system.

7" USB VESA 75 Multi-Point Capacitive Touch Display

Designed along with the leader in transportation/taxi electronics, now from Mimo Monitors is a modified and improved 7" Monitor with a VESA 75 mount. The Mimo UM-760C-SMK adds the following features to its popular line of 7" displays

- Fully enclosed metal back with VESA75 pattern for the ultimate in secure and rugged mounting
- Rear facing speakers using audio over USB
- Adjustable backlight over USB interface
- Along with the standard features of the UM760 line of products
- The responsiveness of multi-point capacitive touch
- Utilizes DisplayLink™ technology that provides video, touch and power over a single USB connection. Now with the addition of audio over the same interface. No separate power supply to worry about
- Can be applied as a secondary customer-facing display in retail POS environments.

Features:

- Capacitive Multi-point Touch Screen
- Utilizes Displaylink™ for power, touch audio, brightness adjust and video over single USB connection
- Compatible with Windows 7 (and higher), Linux, Chrome, and Mac OS*

Applications:

- Transportation
- POP/POS
- Secondary screen for productivity
- Gaming and entertainment
- Light industrial shop-floor automation
- Digital Signage
- Video Conferencing

* With purchase of Mac touchscreen driver

Product Specifications

DISPLAY SECTION	Display	7" diagonal	
	Resolution	1024x600	
	Luminance, White	250 CD/m2	
	Contrast ratio	700:1	
	Aspect Ratio	16:9	
	Viewing angles	75/75/70/75	
VESA Multi-Point Captive Touch	Touch Panel	Capacitive Multi-point	
	Supports	Windows, Linux and Mac OS	

Photos



Mimo Monitors

743 Alexander Rd. Suite 15
Princeton, NJ 08540

info@mimomonitors.com

Sales: **1-855-YES-MIMO (937-6466)**