

nScan® 940gt

The right scanner for the job.

40ppm ►►

nScan® 940gt
40ppm ADF Scanner
Model #DS940GT-AS
\$749.00

Nuance®
Power PDF
Software

45-Day Free Trial



Saves Time and Effort

We make scanning easy. AmbirScan ADF-gt software provides 9 scan profile buttons.

Introducing the nScan® 940gt

Fast and powerful, the nScan 940gt with AmbirScan ADF-gt software is the ideal professional-grade image capture device for any environment. With a compact footprint, assignable profiles & buttons, scan to most Microsoft programs and the ability to scan insurance and ID cards, the 940gt is precise and accurate, making scanning easy.

Save scans as PDFs, TIFs or JPGs to your local computer or popular Cloud services such as: DropBox, EverNote, Microsoft OneDrive and Google Drive.

Ideal industries:



Healthcare



Insurance



Banking & Finance



Real Estate
& Construction



Professional Services
& Consulting



Government
& Legal



©2018 Ambir Technology, Inc. All rights reserved. The Ambir logo and nScan are registered trademarks of Ambir Technology, Inc. Features, specifications and bundled software application(s) and/or version numbers of software applications are subject to change without notice. Windows is a registered trademark of Microsoft Corporation in the United States and other countries. All trademarks and registered trademarks are the property of their respective owners.

nScan® 940gt

Versatility to do More

The nScan 940gt holds up to 80 pages at a time and can scan 40 pages per minute. Powerful imaging hardware lets you capture double-sided images that are crisp and clean for fast, true-to-life scans. And with the ability to handle insurance and ID cards with ease, the 940gt is the perfect answer to all your scanning needs.

Handles High Volume

Ultrasonic Detection ensures precision scanning. Designed for high volumes, the nScan 940gt can process up to 6,000 pages per day.

Broad Compatibility

The included TWAIN driver ensures compatibility with thousands of software applications and hardware systems.

Assignable Profile & Buttons

AmbirScan ADF-gt starts with nine scanning profile buttons assigned to easily selectable buttons on the scanner. From there you can customize the default scanning profiles, create additional profiles for your specific needs and export scanning profiles to colleagues.

Collapsible document trays ensure the ImageScan Pro 940gt fits on even the most crowded desks.



Every Ambir scanner comes with comprehensive, U.S.-based phone & online chat support.

Out of the box ability to scan crisp clean images, with advanced settings available for the most difficult scan jobs.

Specifications

Scanning Speed

40 ppm/80 ipm (300 dpi, Color/Greyscale/B&W modes, Letter)

ADF Capacity

80 sheets (A4/Letter, 70 g/m² or 18 lb.)
Note: Maximum ADF capacity varies, depending upon paper weight.

Scanning Features

"Batch" Document Scanning.

Combine multiple documents into one large scanning job while still keeping your files separated and organized. Document separation options are available and easy to use with AmbirScan ADF-gt which separates files using blank pages, codes, and other options.

Auto-Name Files.

Uses OCR technology to recognize a keyword and characters to auto-name the file. Ideal for scanning invoices and other documents received by mail as well as quick scan jobs that require fast and easy naming.

Product Dimensions & Weight

(L x W x H) 12.4" x 26.8" x 9.4"
(316 mm x 680 mm x 239 mm)

9.2 lbs. (4.2 kg)

Paper Thickness / Card Scan

7 to 110lb (27 ~ 413 g/m²) / 1.25 mm

Acceptable Paper Sizes

4 to 28 lb. (50 to 105 g/m²) Weight for ADF

Daily Duty Scans (sheets)

Up to 6,000

Optical Resolution

Up to 600 dpi

Scan Modes

Auto, Color (input 48-bit/output 24-bit)
Grayscale (input 16-bit/output 8-bit)
Black & White (1-bit)

Warranty

3 Year Limited Warranty

TWAIN Compliant

Energy Star Certified

Kensington Lock Slot