

IN134

InFocus

The Superpowered Projector Designed for Use with Google Chromecast and Other Devices

Part #: IN134

The InFocus IN134 XGA projector combines stellar image performance, long-life lamp and low cost with the ability to create a more powerful and dynamic education experience. Simply insert your Google ChromeCast, Intel Computer Stick, Android solution, or other device into the projector's TechStation internal HDMI 1.4 bay and turn your projector into an all-in-one classroom solution.

Key Features

- ◆ XGA (1024 x 768) resolution
- ◆ TechStation lets you customize your projector with the devices you already use
- ◆ Powered HDMI for mobile charging and device power
- ◆ 28,500:1 contrast ratio and up to 4000 lumens for depth of image and life-like colors
- ◆ Long life lamp of up to 15,000 hours
- ◆ Class-leading, whisper-quiet design



Customize your projector using TechStation

With an HDMI port and multiple ways to connect your devices, the TechStation superpowers your projector and enables more effective learning by working seamlessly with the tools you already use. After connecting your device, close up the TechStation's lid to create a streamlined, all-in-one solution for streaming audio and video.

IN130 Series projectors work with:

- ◆ Google ChromeCast Ultra
- ◆ Intel Computer Stick
- ◆ Asus Chromebit
- ◆ Amazon Fire TV Stick
- ◆ Android stick

- ◆ And more HDMI-supported devices to enable casting, streaming, and wireless



Quietest Projector in its Class

Make sure students always hear the lessons, not the fans. With only 21dB in eco mode, IN134 projector was designed to be quieter, with Smooth Flow fan technology, a cooling-efficient enclosure, and silent bearings.

Save Energy with Value that Lasts

IN130 projectors are designed to fit your budget go the distance with ultra-long lamp life of up to 15,000 hours and no filters to clean or replace. Unlike other imaging technologies, the TI DLP® chip ensures no image decay over time so your projector lasts longer. Activate Dynamic Mode to dim the image

when not in use, and save even more money over the life of the projector.

Over 1 Billion Colors

BrilliantColor™ DLP imaging technology lets images shine with over 1 billion colors that ensure life-like color accuracy and eye-catching presentations. Get better, brighter images on whiteboards, blackboards, or beige walls, in any light.

Easy to Install and Manage

Quickly and simply install and manage your projector over your school's network with free [ProjectorNet 4.1 software](#) from InFocus, or choose to utilize Crestron Roomview or AMX Device Discovery.

Engage Audiences from Every Angle with 3D

Bring content to life with support for multiple forms of 3D -- including Blu-Ray, 3D broadcasting, videos games and PC connectivity. All your audience needs are [144Hz DLP Link 3D glasses](#) (sold separately).



Specifications*

Projector	IN134
Resolution – Native	XGA (1024 x 768)
Display Technology	DLP
Video Standard Compatibility	NTSC, NTSC 4.43, PAL, PAL-M, PAL-N, SECAM, 480i, 480p, 576i, 576p, 720p, 1080i, 1080p
Speakers	Mono 10W x 1
Lamp Brightness	4,000 lumens
Lamp Brightness – Eco Mode	3,200 lumens
Lamp Life	5,500 hours
Lamp Life – Low Power	10,000 hours

Projector		IN134
Lamp Life – Dynamic Mode		15,000 hours
Lamp Power		220W
Lamp Power – Eco Mode		145W
Contrast Ratio		28,500:1
Color Wheel		High Speed 6 Segment RYGCWB
Number of Colors		1.07 billion
Synch Scan Frequency – Horizontal		31.5 ~ 97.6 KHz
Synch Scan Frequency – Vertical		56 - 120 KHz
Aspect Ratio		4:3
Aspect Ratio Compatibility		16:9, 16:10, 2.35:1, 1:1, 2:1, 13:9, 15:9, 5:4
Projection Lens F-Stop – Minimum		2.41
Projection Lens F-Stop – Maximum		2.53
Lens Type		Manual focus
Image Size – Minimum		22 in
Image Size – Maximum		244 in
Projection Offset		115% +/- 5% V
Keystone Correction		± 40°V
Connectors – Inputs		3.5mm audio, Composite video, VGA, HDMI 1.4a x3 (with 1.4a 3D support), USB-A (TechStation Connection)
Connectors – Outputs		3.5mm audio output, Monitor out (VGA)
Control		RS232, IR Remote
Audible Noise – Eco Mode		< 21 dBA at 0°F / -17.8°C
Included Accessories		Power cord, Remote, HDMI Cable, Documentation, User Manual (CD)
3D Support		1080p @ 60Hz, All HDMI 1.4a 3D formats, DLP Link 3D glasses required
Power Consumption		300.0W max
Power Consumption – Standby Mode		1.8W max
Power Consumption – Low Power Standby		0.5W max
Power Consumption – Eco Mode		220.0W max
Power Standard		AC 100 to 240V, 50/60
Operating Conditions		41 to 104°F at 0 to 10000 ft / 5 to 40°C at 0 to 3048 m
Documentation Languages		English, French, German, Spanish, Italian, Norwegian, Dutch, Simplified Chinese, Korean, Swedish, Russian, Finnish, Arabic, Indonesian, Portuguese
Menu Languages		English, French, German, Spanish, Italian, Norwegian, Dutch, Simplified Chinese, Traditional Chinese, Korean, Russian, Finnish, Polish, Turkish, Danish, Arabic, Indonesian, Portuguese, Vietnamese, Czech, Romanian, Hungarian, Malay, Hindi, Filipino, Farsi, Japanese, Thai
Security Features		Kensington lock port
TechStation		Works with Google Chromecast, Chromecast Ultra, Amazon Fire Stick, Android TV Stick, InFocus SimpleShare, Asus Chromebit, Intel PC Stick, Raspberry PI, EZ Cast Pro Dongle and other HDMI devices

Throw and Zoom	
Throw Distance – Minimum	1 m
Throw Distance – Maximum	12 m
Throw Ratio – Minimum	1.94:1
Throw Ratio – Maximum	2.16:1

Shipping	
Product Dimensions	4.9 x 9.3 x 12.3 in / 124.5 x 236.2 x 312.4 mm
Product Weight	7.1 lbs / 3.2 kg
Shipping Dimensions	7.7 x 13.3 x 15.7 in / 195.6 x 337.8 x 398.8 mm
Shipping Weight	9.9 lbs / 4.5 kg

* Product specifications, terms, and offerings are subject to change at any time without notice.

Accessories

- SimpleShare Presentation System (INA-SIMPS1)
- Universal Projector Ceiling Mount (PRJ-MNT-UNIV)
- 1 Year Extended Warranty for IN1XX Projectors (EPW-PJV1)
- DLP Link 3D Glasses by XPAND (X103-EDUX3-R1)
- Soft Carry Case for Value Projectors (CA-SOFTVAL-2)

SimpleShare (INA-SIMS1)
SimpleShare Touch Presentation System (INA-SIMINT1)
SimpleShare Transmitter (INA-SIMTM1)
SimpleShare Receiver (INA-SIMRC1)
SimpleShare Transmitter with Paired USB Touch Adapter (INA-SIMTTM1)
SimpleShare Interactive Receiver (INA-SIMRINT1)
SimpleShare Charging Station (INA-SIMCH1)
LiteShow 4 DB+ Dual Band Wireless Adapter (INLITESHOW4DB+)
2 Year Extended Warranty for IN1XX Projectors (EPW-PJV2)