

GCS1816HKITU

16-Port USB HDMI KVMP Switch with USB Cable Sets (TAA Compliant)



- Controls up to 16 HDMI® sources while sharing 2 additional USB 2.0 devices
- Supports up to 1080p (1920 x 1200) HD video resolution
- Cascade up to 2 levels¹ - control up to 256 computers from a single console
- Features 2 built-in USB 2.0 ports² for USB peripheral sharing
- Multi-display feature allows viewing of up to 8 monitors when stacking up to (8) GCS1816H together

16-Port HDMI KVMP Switch with USB KVM Cable Set

IOGEAR's 16-port USB HDMI KVMP Switch with USB Cable Set allows you to control and access up to 16 computers from a single USB keyboard, USB mouse, and an HDMI monitor console. Using the included USB cables, experience high definition video resolution to 1080p (1920 x 1200) while sharing USB 2.0 peripherals and listening to 2.1 stereo surround sound.

- Controls up to 16 HDMI® sources while sharing 2 additional USB 2.0 devices
- Supports up to 1080p (1920 x 1200) HD video resolution
- Cascade up to 2 levels¹ - control up to 256 computers from a single console
- Features 2 built-in USB 2.0 ports² for USB peripheral sharing
- Multi-display feature allows viewing of up to 8 monitors when stacking up to (8) GCS1816H together
- Independent KVM and USB focus switching
- Supports 2 level password protection security for On-Screen Display (OSD)
- OSD Backup/Restore configuration and user profile information
- Broadcast Mode sends commands to all connected computers
- Auto Scan Mode monitors connected computers
- HDMI input connectors equipped with screw lock for secure connection
- Rack mountable in a 19" (1U) system rack
- Multi-platform OS support - Windows®, Mac, Oracle® Solaris and Linux®
- Easy-to-operate computer selection via front panel LEDs, intuitive multi-lingual On-Screen Display (OSD), and hotkeys

- Video DynaSync³ - An exclusive IOGEAR technology, optimizes resolution when booting-up or switching between ports
- Console mouse port emulation & bypass feature supports most mouse drivers and multifunction mice
- Complete keyboard emulation for error-free booting
- Mac/Sun keyboard support and emulation⁴
- Multilingual OSD supports English, German, Japanese, Chinese, Spanish, Russian, and French
- Multilingual keyboard mapping supports English (US), English (UK), German, Japanese, Traditional Chinese, Spanish, Korean, and French
- HDCP compatible
- Firmware upgradable


¹Cascade only with another GCS1816H for control over 256 computers

²The built-in USB 2.0 hub cannot be accessed from sources on the second or third level of a cascaded installation

³IOGEAR's DynaSync Display Emulation Technology provides the DDC support for Windows® 7

⁴PC keyboard combinations emulate Mac/Sun keyboards; Mac/Sun keyboards work only with their own OS





Requirements

- **Console:**
 - HDMI display
 - Standard 104 key wired USB keyboard
 - Standard 2 or 3 button wired USB mouse
 - Speakers (optional)
 -
- **Source devices:**
 - HDMI output
 - USB Type-A port
 - Speaker ports (optional)
 -
- **Operating Systems:**
 - Windows Vista®, Windows® 7, Windows® 8, Windows® 8.1, Windows® 10
 - Mac OS 9 to 10.x
 - Oracle® Solaris
 - Linux®, Unix and other USB supported systems¹

Package Contents

- 1 x 16-port USB HDMI KVMP Switch
- 16 x Custom 6ft. USB HDMI KVM Cable Sets
- 1 x Firmware Upgrade Cable
- 1 x Power Adapter
- 1 x Foot Pad Set (4 pcs)
- 1 x Quick Start Guide
- 1 x Rack Mounting Kit

¹Additional drivers and support may be needed

Specifications

Function	GCS1816HKITU		Dimensions	GCS1816HKITU	
Computer Connections			Unit Dimensions		
Direct	16		Height	1.75" (4.45cm)	
Daisy Chain or Cascading	256 (via Cascade)		Depth	10" (25.4cm)	
Port Selection	OSD, Hotkey, LED Pushbutton		Length	17" (43.18cm)	
Console Connectors			Unit Package Dimensions		
Monitor	1 x HDMI Female		Width	22.75" (57.79cm)	
Keyboard	1 x USB Type-A Female		Height	5.25" (13.34cm)	
Mouse	1 x USB Type-A Female		Depth	20.75" (51.44cm)	
Audio	2 x 3.5mm Stereo Jack Female (1 x Front Panel; 1 x Rear Panel)		Master Carton		
CPU Connectors			Width	22.75" (57.79cm)	
Monitor	16 x HDMI Female		Height	5.25" (13.34cm)	
Keyboard & Mouse	16 x USB Type-B Female		Depth	20.25" (51.44cm)	
Audio	16 x 3.5mm Stereo Jack Female		Master Carton Qty.	1	
Switches			Weight		
F/W Upgrade	1 x Slide Switch (Front Panel)		Master Carton Wt.	21.65lb (9.85kg)	
Port Selection	16 x LED Pushbutton (Front Panel)		Unit Pack Wt.	21.65lb (9.84kg)	
Connectors			Unit Wt.	8.8lb (4kg)	
Power	1 x DC Jack				
USB	2 x USB 2.0 Type-A Female (1 x Front Panel; 1 x Rear Panel)				
LEDs					
USB Peripherals	16 (Green)				
On Line	16 (Orange)				
Power On	1 (Dark Green)				
Emulation					
Keyboard	USB				
Mouse	USB				
Video Resolution	480i, 480p, 720p, 1080i, and 1080p (HDTV) / 1920 x 1200 @60Hz				
Scan Interval	1 - 255 Seconds (Default: 5 sec)				
Power Consumption	DC 5.0V; 12.2W				
Environment					
Operation Temperature	0 - 50C				
Storage Temperature	-20 - 60C				
Humidity	0 - 80% RH; Non-condensing				
Housing					
Case	Metal				
Cable Length	16 x 6 feet custom USB HDMI KVM cable				