

## 17" HD Rackmount KVM Console - Dual Rail

Product ID: RKCOND17HD



Providing centralized control of your single PC or dozens of servers, this dual rail rackmount KVM console also gives you easy access to and visibility of your system while it's mounted in a server rack or cabinet.

### Dual Rail Design

The dual rail KVM console design maximizes space in your datacenter's rack cabinets by allowing the LCD monitor and the keyboard/mouse to move separately from each other. You can tuck the keyboard away while the display stays active, allowing you to conveniently monitor your computer through closed glass or mesh rack cabinet doors.

### High Definition LCD Monitor

The 1080p KVM console is 17.3" and LED back-lit, for low power consumption. It supports high definition resolutions up to 1920x1080 providing sharper video performance.

### Digital & Analog Support

Whether you are running a multi-port KVM with an analog display or a single port KVM with a high definition display, this DVI/ VGA KVM console can support both signals.

### **Simple Setup**

This KVM console comes with everything you need to set up:

- ✓ 1 Audio Cable
- ✓ 1 Set of KVM Cables (USB/VGA)
- ✓ 2 Rear Mounting Brackets
- ✓ M5 Cage Nuts and Screws

Once your KVM console is mounted to your rack, you can use the USB port on the front to easily connect any USB compatible peripheral such as a fingerprint scanner or mousethumb drive.

StarTech.com offers a wide selection of KVM consoles to help you access your systems more efficiently without the expense and clutter of extra peripherals. This dual rail KVM console is backed by a 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Large server farms
- Co-location facilities

### Features

- Slide the rackmount monitor and keyboard/mouse independently with dual-rail KVM console design
- 1080p KVM console supports high-definition resolutions up to 1920x1080
- Supports both digital and analog connections with DVI and VGA ports
- Set up easily with included brackets, cables and screws
- Connect a fingerprint scanner or other peripheral to the USB port on front of KVM console

<b>Hardware</b>	Warranty	2 Years
	Audio	Yes
	Cables Included	Yes
	Display Size	17.3"
	KVM Ports	1
	Number of Monitors Supported	1
	Panel Type	Active Matrix TFT LCD
	PC Interface	USB
	PC Video Type	DVI+VGA
	Rack-Mountable	Yes
	U Height	1U
<b>Performance</b>	Aspect Ratio	16:9
	Brightness	250 cd/m <sup>2</sup>
	Color Depth	18-bit, 262,144 colors
	Contrast Ratio	650:1
	DVI Support	Yes
	Hot-Key Selection	Yes
	Maximum Analog Resolutions	1920 x 1080 @ 60Hz
	Maximum Digital Resolutions	1920 x 1080 @ 60Hz
	MTBF	Approx. 44230 hrs.
	On-Screen Display	No
	Pixel Pitch Support	0.199 x 0.199 mm
	Response Time	8 ms
	Supported Resolutions	1024×576 1152×648 1280×720 1366×76 1600×900 1920×1080
	Viewing Angle	140° (H), 120° (V)
	Wide Screen Supported	Yes
<b>Connector(s)</b>	Console Interface(s)	1 - VGA (15 pin, High Density D-Sub) Female Output 2 - USB Type-A (4 pin) USB 2.0 Female 1 - DVI-D (25 pin) Female Output

	Host Connectors	<ul style="list-style-type: none"> <li>1 - 3.5 mm Stereo Audio Female Output</li> <li>1 - VGA (15 pin, High Density D-Sub) Male Input</li> <li>1 - DVI-D (25 pin) Female Input</li> <li>1 - USB Type-B (4 pin) USB 2.0 Female</li> <li>1 - 3.5 mm Stereo Audio Female Input</li> </ul>
<b>Software</b>	OS Compatibility	OS independent; No software or drivers required
<b>Indicators</b>	LED Indicators	<ul style="list-style-type: none"> <li>1 - Power</li> <li>1 - Num Lock</li> <li>1 - Caps Lock</li> <li>1 - Scroll Lock</li> </ul>
<b>Power</b>	Input Current	1A
	Input Voltage	100 ~ 240 AC
	Power Consumption (In Watts)	19.4W
	Power Source	International Power Cords
<b>Environmental</b>	Humidity	0~80% RH Non-condensing
	Operating Temperature	0~40 Celsius Degree
	Storage Temperature	-20~60 Celsius Degree
<b>Physical Characteristics</b>	Cable Length	<ul style="list-style-type: none"> <li>USB and VGA Combo Cable 1.2M</li> <li>3.5in Audio cable 1.8M</li> </ul>
	Color	Black
	Enclosure Type	Steel
	Maximum Mounting Depth	39.4 in [1000 mm]
	Minimum Mounting Depth	25.6 in [649.8 mm]
	Product Height	1.7 in [44 mm]
	Product Length	28.6 in [727 mm]
	Product Weight	26.5 lb [12 kg]
	Product Width	18.9 in [480 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	3.1 lb [1.4 kg]
<b>What's in the Box</b>	Included in Package	<ul style="list-style-type: none"> <li>1 - LCD Console</li> <li>2 - Rear Mounting Brackets</li> <li>1 - Set of KVM Cables (USB/VGA)</li> </ul>

- 1 - Audio Cable
- 1 - Firmware Update Cable
- 8 - M5 Cage Nuts
- 8 - M5 Screws
- 5 - Power Cords (NA, JP, UK, EU, ANZ)
- 1 - Quick-Start Guide

---

Product appearance and specifications are subject to change without notice.