

USB C Multiport Video Adapter - 4K 60Hz UHD Portable 5-in-1 USB Type C to HDMI 2.0, Mini DisplayPort, VGA or DVI (1080p) - 95W PD Passthrough - Cable Management - Aluminum

Product ID: CDPVDHMDPDP



This USB-C multiport video adapter offers a portable solution for connecting your USB Type-C laptop to a VGA, DVI, HDMI or Mini DisplayPort (mDP) display. It features USB Power Delivery, so you can power your laptop while outputting video using the same USB-C port.

Power and Video in One Port

This USB-C adapter supports USB Power Delivery up to 95 watts and features an additional USB-C port. You can charge your laptop using its USB-C power adapter, even while you output video. Many laptops support charging through a USB-C port with Power Delivery, check your specifications to confirm compatibility.

All-in-One Video Connectivity with Travel in Mind

Carry one adapter instead of four. This versatile 4-in-1 monitor adapter lets you connect your USB-C laptop to any display. With its durable aluminum enclosure and a magnetic retainer that secures the breakout cable in place while you're not using it, the adapter is rugged enough to carry in your travel bag.

Astonishing Picture Quality

The HDMI and mDP outputs support UHD 4K resolutions, providing four times the picture quality of high-definition 1080p. All of the outputs (HDMI, mDP, VGA, DVI) support high-definition resolutions up to 1920 x 1200. The adapter is compatible with USB-C DP Alt Mode devices.

Stylish Connectivity

The USB-C adapter has a Space Gray trim and built-in USB-C cable designed to match your Space Gray MacBook, or MacBook Pro.

CDPVDHMDPDP is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect to virtually any display while traveling
- Connect a MacBook or USB-C laptop to a VGA, DVI, HDMI or mDP display
- Connect a secondary monitor to your Space Gray MacBook or USB-C laptop

Features

- **5-IN-1 MULTIPORT USB-C VIDEO ADAPTER:** USB-C DP Alt Mode to any one of 4K 60Hz HDMI 2.0/mDP 1.2 or 1080p VGA/DVI with HDCP 2.2/1.4, Thunderbolt 3 compatible, 95W Power Delivery Pass-Through, Space Gray
- **95W PD 3.0 PASS-THROUGH:** Use a USB-C power adapter to charge laptop (Ultrabooks & workstations) up to 95W; prevents video drop/flickering when power is added/removed on PD 3.0 laptops like MacBook Pro
- **COMPATIBILITY:** USB-C display adapter for TB3 MacBook Pro/Air, Dell XPS/Precision/Latitude, Lenovo ThinkPad X1 Carbon/Extreme, Surface Laptop 3/Surface Book 3, HP EliteBook/Spectre/ZBook, Chromebooks
- **TESTED & VERIFIED:** USB Type-C adapter tested @ 4K 60Hz HDMI 2.0/Mini DisplayPort or 1080p VGA/DVI for compatibility w/ TVs, monitors & projectors like Dell, Asus, Acer, LG, Samsung, Sharp, Sony, Epson
- **EASY TO USE:** Durable aluminum space gray housing w/ magnetically-secured hideaway cable wrap; supports driverless plug-and-play setup, and is compatible with Windows / macOS / Linux / Chrome OS

Hardware	Warranty	3 Years
	Active or Passive Adapter	Active
	Adapter Style	Adapters
	AV Input	USB-C
	AV Output	DVI-I (Digital Only) - Single-Link HDMI - 1.4 VGA Mini DisplayPort - 1.2
	Chipset ID	Parade - PS176 VIA/VLI - VL102 ITE -IT6516
Performance	Audio Specifications	HDMI - 7.1 Channel Audio DVI - No Audio Support VGA - No Audio Support Mini DisplayPort - 5.1 Channel Audio
	Maximum Analog Resolutions	1920 x 1200 @ 60Hz
	Maximum Cable Distance To Display	49.9 ft [15.2 m]
	Maximum Digital Resolutions	4096 X 2160 @ 24Hz or 3840 X 2160 @ 60Hz (HDMI) 4096 X 2160 @ 60Hz (mDP)
	Supported Resolutions	Maximum HDMI output: 4096 X 2160 @ 24Hz or 3840 X 2160 @ 60Hz Maximum mDP output: 4096 X 2160 @ 60Hz Maximum DVI and VGA output: 1920 x 1200 @ 60Hz <i>Lower resolutions and refresh rates may also be supported</i>
	Video Revision	HDMI 2.0 DisplayPort 1.2
	Wide Screen Supported	Yes
	Connector(s)	Connector A
Connector B		1 - Mini-DisplayPort (20 pin) Female Output 1 - VGA (15 pin, High Density D-Sub) Female Output 1 - DVI-I (29 pin) Female Output

		1 - HDMI (19 pin) Female Output
		1 - USB-C (24 pin) USB Power Delivery only Female Input
Special Notes / Requirements	Note	<p>Only one video output is supported on the video adapter at a time, if multiple connections are made, only one of the outputs will function</p> <p>Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling</p> <p>Your laptop may have specific requirements for charging. This USB-C multiport adapter supports USB Power Delivery 3.0, up to 95W. When using your laptop's USB-C power adapter, the multiport adapter powers both the adapter and your laptop - with up to 85W charging available for laptop charging. For more information on your laptop's charging requirements, refer to the manufacturer of your laptop.</p>
Power	Laptop Charging via Power Delivery	85W
	Power Consumption (In Watts)	10W
	Power Delivery	95W
	Power Source	USB-Powered
Environmental	Humidity	0~95% RH
	Operating Temperature	0°C to 45°C (32°F to 113°F)
	Storage Temperature	0°C to 60°C (32°F to 140°F)
Physical Characteristics	Accent Color	Black & Space Gray
	Cable Length	4 in [101 mm]
	Color	Black
	Material	Aluminum
	Product Height	0.7 in [1.8 cm]
	Product Length	4.3 in [10.9 cm]
	Product Width	2.2 in [57 mm]
	Weight of Product	4.5 oz [128 g]
Packaging Information	Package Height	1.2 in [30 mm]
	Package Length	6.9 in [17.5 cm]
	Package Width	5.6 in [14.2 cm]
	Shipping (Package) Weight	0.5 lb [0.2 kg]

What's in the Box	Included in Package	1 - Travel A/V Adapter
--------------------------	---------------------	------------------------

Product appearance and specifications are subject to change without notice.