

Kanguru SS3™

SuperSpeed USB 3.0 with Physical Write Protect Switch

The Kanguru SS3 is one of the fastest solid performance SuperSpeed USB3.0 flash drives on the market, with read speeds of up to 410MB/sec and write speeds of up to 320MB/sec. It features USB3.0 speeds while maintaining compatibility with USB2.0 so you can use it on virtually any computer. Its small, durable aluminum design is compact and lightweight, and provides lightning-fast transfer rates that make it the perfect solution for those in a hurry who want the convenience of carrying data files from place to place.

Kanguru SS3 includes a built-in physical write-protect switch that provides more safety and convenience than other USB flash drives. Protect your data and safely connect to any computer with the switch to “read-only”, and you can be assured that your files are protected and cannot be overwritten. This feature also prevents viruses and malware from having any chance of infecting the drive. Flip it back and you can make adjustments to your files just as you would with any other flash drive.

The Kanguru SS3 comes in capacities of 16GB, 32GB, 64GB, 128GB and 256GB providing plenty of room to store and transport your files in record time.

FEATURES/BENEFITS

- SuperSpeed USB3.0
- Physical Write-Protect Switch
- Windows “Ready Boost” Compatible
- Requires NO Admin Privileges
- Simple Driverless Setup
- High-Strength Aluminum Design
- Custom Engraving Available
- Works With Virtually Any Computer



The Kanguru SS3 flash Drive is TAA Compliant

Customize your Kanguru SS3™
High Performance USB 3.0 Flash Drive

[Learn More](#)

* Please note: Due to Microsoft's End-of-Support for Windows XP, Kanguru is ending support for its line of products running on the Windows XP platform. (see our full disclaimer on kanguru.com)



Model Number:
KF3WP



**Physical
Write-Protect
Switch**



**SuperSpeed
USB 3.0**

MODEL NUMBER	KF3WP Series
CAPACITIES	16GB, 32GB, 64GB, 128GB, 256GB
INTERFACE	USB3.0 (USB2.0 & 1.1 Compatible)
DATA TRANSFER RATE	Max Read: 410MB/sec Max Write: 320MB/sec
OS COMPATIBILITY	Windows XP*/Vista/7 Mac OSX 10.1.5+ Linux (Kernel 2.4.1 and Above, must be mounted) Linux Ubuntu 10+ Red Hat 5+ Open SUSE11+
MEMORY TYPE	Solid State MLC NAND Flash
WRITE CYCLES	10,000 Write Cycles / Block
DATA RETENTION	10 Years or More
OPERATING TEMP	0° C - 70°C
HUMIDITY RANGE	20% - 90%
SHOCK RESISTANCE	1000G Max
VIBRATION	15G Peak to Peak Max
WEIGHT	14g
DIMENSIONS	77.21 mm L x 19.44 mm W x 8.96 mm H 3.039" L x 0.765" W x 0.352" H
POWER	Typical Read: 5 VDC @ 100mA Typical Write: 5 VDC @ 105mA



KANGURU™
Secure. Anytime. Anywhere.

FOR MORE INFORMATION,
PLEASE CONTACT:

Kanguru Solutions
sales@kanguru.com
1-888-KANGURU
www.kanguru.com