



Dual Monitor Mount Professional Touch Adjust

DMPRO2DTA-3N

SKU: 8605LA

Position dual monitors quickly and easily with the Professional Dual Touch Adjust Monitor Desk Mount from V7. Made from premium quality aluminum and cold rolled steel for durability with black matte finish, the mount can hold up to 32" displays and 17 lbs (8 kg). No more crawling under the desk as this mount installs completely from the top with easy no screw arm installation making setup the quick and easy. Featuring an advanced cable management system to keep video and power cables neatly tucked away and out of sight, and included clamp and grommet mounting options, it's perfect for virtually any workstation. The height adjustment and independently adjustable arms enable multiple viewing angles, so you can position your monitor where it's most comfortable to use. Additionally, the mount has a quick-release VESA plate to make installation easy and is backed by a 5-year warranty.

- Dual monitor mounting arm for up to 32" (81.28cm) displays
- Installs entirely from above the desk surface with screwless arm installation and Quick release VESA plate for fast and easy setup
- Free tilt and 360° swivel design with height adjustable stand and arm for flexible viewing angles and better ergonomics
- Cable management system keeps cables out of the way or organized
- Both clamp and grommet mounting options are included

General

Sku: 8605LA
 Model: DMPRO2DTA-3N
 UPC: 662919103649
 Warranty: 5 years
 Compliance: RoHS
 Country Of Origin: China
 Package Type: 4 Color Box
 Package Includes: Product, Hardware, User's Guide

Design

Display Size (per display): 17" to 32" Displays
 Mount Type: Desk
 Material: Steel, Aluminum, Plastic

Package Dimensions

Package Dimensions (L/W/H): 400 x 215 x 155 mm
 (15.75 x 8.46 x 6.1 in)
 Package Weight: 13.8 lbs (6.26 kg)

Product Dimensions

Product Dim (L/W/H): 1066 x 129 x 697 mm (41.97 x 5.08 x 27.44 in)
 Product Weight: 12.57 lbs (5.7 kg)

California Prop 65

No warning required

Technical

VESA Mount: 100 x 100 mm, 75 x 75 mm
 Pan: +90°~-90°
 Height Adjustment: 7.09-24.41 in (180-620 mm)
 Weight Limit (per display): 17.64 lbs (8 kg)