


27BK550Y

BK550 SERIES

KEY FEATURES

- 27" FULL HD (1920 x 1080) IPS panel
- Colour Calibrated
- 4-Screen Split
- Tilt, Pivot, Swivel and Height Adjustable Stand
- On-Screen Control



PRODUCT FEATURES

PANEL

Screen Size	27" (69cm)
Panel Technology	IPS
Aspect Ratio	16:9
Resolution	1920x1080
Brightness	250 cd/m2 (Typ) 200 cd/m2 (Min)
Contrast Ratio	1000:1
Response Time	5ms (High)
Viewing Angle (H x V)	178° x 178°
Colour Depth	16.7M colours
Surface Treatment	Anti glare ,3H

CONNECTIVITY

Input (Rear)	Display Port (ver1.2)
Digital	HDMI (ver1.4), DVI
Analogue	D-Sub
Output (Rear)	USB 2.0 (1 up 2 down)
Audio	Headphone Out 2 CH Stereo, 1.2W x 2ea PC Audio In

ENVIRONMENT CONDITIONS

Operation Temperature	0°C - 40 °C
Operation Humidity	Less than 80 %

ACCESSORIES

Power Cable, Display Port

WARRANTY

3 Years (Parts & Labour)

PHYSICAL SPECIFICATIONS

With stand (WxDxH)	622mm x 240mm x 402mm
Without stand (WxDxH)	622mm x 58mm x 372mm
With stand Weight (kg)	7.2 kg
Without stand Weight (kg)	5.1 kg
Carton (WxHxD)	707mm x 556mm x 186mm
Packed Weight (kg)	10 kg
VESA™ Standard Mount Interface	100mm x 100mm

STANDARD (CERTIFICATION)

Comparative Energy Consumption	94 kWh / year
Star Rating	5 (Stars)
Active Standby	0.24W
Safety	CB Scheme, RCM
ErP/US EPA	No / Yes (7.0)
EMC	RCM, Class (B)

SPECIAL FEATURES

Plug & Play, Dual Control, Off Timer, Six Axis Control, Super Resolution+ OSC (On Screen Control / Screen Split), Colour Calibrated.

Stand	Tilt -2° (Front) ~ 35° (Rear) Swivel '0°~355° (±5°) Pivot Bi-directional, 90° Mini PC Bracket Ready
-------	--

POWER

Power Supply	100 ~ 240V, (50/60Hz)
Power Consumption	20.3W (EPA), 27.4W (typ)
Typical / Smart Energy Saving on	0.5W
Power Off	0.3W
Power Type	Built-in



*LED LCD Monitors combine LCD screen with LED back light technology

Disclaimer: All product specifications correct at time of printing. Specifications may change without prior notice.