

32QK500-W.AUSQ

32" QHD IPS FreeSync Monitor

32" QHD (2560 x 1440) IPS Display

Radeon FreeSync™ Technology

On Screen Control / Screen Split

Multiple Input (DP x 1, mDP x 1, HDMI x 2)

KEY FEATURES

PRODUCT INFO



PICTURE QUALITY

Screen Size	32" Flat
Panel Type	IPS
Color Gamut (Typ.)	NTSC 72% (CIE1931)
Color Depth(Number of Colors)	1.07B
Pixel Pitch(mm)	0.2727 x 0.2727 mm
Response Time (GTG)	8ms (GtG at Faster)
Refresh Rate	75Hz
Aspect Ratio	16:9
Resolution	2560 x 1440
Brightness	250 cd/m²(Min.), 300 cd/m²(Typ.)
Contrast Ratio	700:1 (Min.), 1000:1 (Typ.)
Viewing Angle	178°(R/L), 178°(U/D)
Surface Treatment	Haze 25%, 3H

INPUT/OUTPUT

HDMI	Yes x 2
DisplayPort	Yes x 1
Headphone Out	Yes
Mini DisplayPort	Yes x 1

POWER

Type	Adapter
Input	100 -240, 50/60Hz
Power Save/Sleep Mode (Max)	Less than 0.5W
DC Off (Max)	Less than 0.3W
Power Consumption (Typ.)	46.0W
Power Consumption (Energy Star)	30.9W
Power Consumption (Max.)	50.0W

SPECIAL FEATURES

Adaptive Sync	RADEON FreeSync™
Black Stabilizer	Yes
Dynamic Action Sync	Yes
Crosshair	Yes
Flicker Safe	Yes
Smart Energy Saving	Yes
Reader Mode	Yes
On Screen Control (OSC)	Yes

DIMENSIONS/WEIGHT

With Stand (WxHxD)	28.5" x 20.4" x 8.7"
Without Stand (WxHxD)	28.5" x 16.7" x 1.7"
Shipping Dimensions (WxHxD)	32.6" x 23.6" x 8.4"
With Stand Weight	12.6 lbs
Without Stand Weight	11.9 lbs
Shipping Weight	19.6 lbs

CABINET / ACCESSORIES

Wall Mount Size (mm)	100 x 100 mm
S/W Install CD	Yes

LIMITED WARRANTY / UPC

Limited Warranty	1 Year Parts and Labor
UPC	719192620711
Country of Origin	China