



RP2MB1.1

RAMPART 1080p IP BULLET CAMERA



1080p RESOLUTION



SEE COLOR NIGHT VISION



WEATHER RESISTANT



H.265 COMPRESSION

RP2MB1.1

RAMPART 1080p IP BULLET CAMERA

SPECIFICATIONS

Camera Type	Bullet Camera
Camera Technology	IP
Image Sensor Size	1/2.7"
Image Sensor Type	Progressive CMOS
Megapixels (Digital)	2 MP
Effective Pixels	1920 x 1080
Lens Size	4.0mm Fixed Lens
Field of View	106°
IR Cut Filter	Yes
Max. User Access	Up to 20 Users
Storage	No Local Storage



NIGHT VISION

Night Vision Range	Up to 98 ft (w/ IR On)
See Color Night Vision	Yes (w/ Min. 0.02 Lux)

IMAGE FEATURES

Video Compression	H.265+, H.265, H.264
Wide Dynamic Range	Yes

REMOTE MONITORING

Use as Standalone	Yes
Compatible Software	Q-See Presidio
Compatible Mobile Devices	Android, iPhone
Compatible Systems	Presidio Series NVR's

RESOLUTION & FRAME RATE

1080p (1920 x 1080)	Up to 25FPS
720p (1280 x 720)	Up to 25FPS
D1 (704 x 576)	Up to 25FPS

POWER

Power Supply	DC 12V 1A PoE
Power Consumption	≤5.5 W

AUDIO

Microphone	No
Speaker	No

PTZ

Pan, Tilt, Zoom	No
-----------------	----

CONNECTIVITY

Connector Types	RJ-45 Ethernet 10/100 Mbps
Wireless	No

PHYSICAL ATTRIBUTES

Weatherproof	Yes
IP Rating	IP67
Body Construction	Plastic
Mounting Hardware	Screws (Wall or Ceiling Mount)
Weight	0.99 lbs
Dimensions	6.4" x 2.5" x 2.5"
Operating Temperature	-22° to 140° F