



THE HIGH-PERFORMANCE PRINTER
FOR THE HOME & OFFICE

PIXMA TS702

COMPACT CONNECTED INKJET PRINTER

PRINT | WIRELESS | MOBILE

KEY FEATURES:



Smartphone Copy¹



Hybrid Ink System



350 Sheet
Plain Paper Capacity



Borderless Photos²



Auto 2-Sided Print



Wi-Fi³ & Ethernet

CONNECTIVITY:



⁴



⁵



CANON PRINT APP

PIXMA TS702 COMPACT CONNECTED INKJET PRINTER

TECHNICAL INFORMATION

PRINT


Print Features	AirPrint, ⁴ Auto 2-Sided (Duplex) Printing, Borderless Printing, ² Black Ink / Color Ink Only Printing (Windows Only), Canon PRINT app, ¹ Document Printing, Easy-PhotoPrint Editor Software/app, ⁶ Google Cloud Print, ⁷ Greeting Cards, Message In Print app, ⁸ Mopria Print Service, ⁵ Photo Printing, PIXMA Cloud Link, ¹ Wireless Printing ³
First Print Out Time (FPOT) ⁹	FPOT (Black): Approx. 10 Seconds FPOT (Color): Approx. 8 Seconds
Print Speed ⁹	4" x 6" Photo: Approx. 21 Seconds (Borderless) ESAT (Black): Approx. 15.0 ipm ESAT (Color): Approx. 10.0 ipm
Number of Nozzles	Color: 3,072 / Pigment Black: 1,024 / Total: 4,096
Print Resolution ¹⁰	Up to 4800 x 1200 dpi
Paper Sizes	3.5" x 3.5," 4" x 4," 4" x 6," 5" x 5," 5" x 7," 7" x 10," 8" x 10," Letter, Legal, U.S. #10 Envelopes
Media Compatibility	Plain: Plain Paper, Canon High Resolution Paper; Super High Gloss: Photo Paper Pro Platinum; Glossy: Photo Paper Plus Glossy II, Photo Paper Glossy; Semi-gloss: Photo Paper Plus Semi-Gloss, Photo Paper Pro Luster; Matte: Matte Photo Paper Other: Greeting Cards, Magnetic Photo Paper, Printable CD/DVD/Blu-ray Discs, Restickable Photo Paper, T-Shirt Transfers, U.S. #10 Envelopes
Paper Capacity	Rear Paper Tray: 100 Sheets of Plain Paper OR Photo Paper: 20 Sheets of 4" x 6" / 10 Sheets of 5" x 7" Front Paper Cassette: 250 Sheets of Plain Paper

GENERAL

General Features	5-Color Individual Ink System, Automatic Replenishment Service (ARS) Capable, Auto Power On / Off, Bluetooth Connectivity, ¹¹ Canon PRINT app, ¹ Canon Print Service, ¹² CREATIVE PARK PREMIUM, ¹³ Wireless Direct Connection, Energy Star [®] Certified, Hybrid Ink System, Standard MIB (Management Information Base) Support, PIXMA Cloud Link, ¹ Quiet Mode, Wireless Connect ¹⁴
Display	2 Line Full-Dot Matrix Display
Voice Service, Smart Assistant & Automation Support	Amazon Alexa, ^{™15} Google Assistant, ^{™15} IFTTT (IF This Then That) Support ¹⁶
Connectivity	Hi-Speed USB, PictBridge / Wireless PictBridge, ¹⁷ Wi-Fi ^{™4} (802.11b/g/n wireless networking, 2.4 GHz), ³ Ethernet (100/10 Base-T), Bluetooth 4.0 (Low Energy) ¹¹
Duty Cycle & Recommended Print Volume ¹⁸	15,000 Pages Recommended Monthly Print Volume: 250 - 1,000 Pages
Software (Windows ^{™19} / Mac ^{™20})	PIXMA TS702 Compact Connected Inkjet Printer Driver, Easy-PhotoPrint Editor Software, ⁶ PosterArtist Lite (Windows Only), ²¹ Master Setup, My Printer (Windows Only), Network Tool, Quick Menu
OS Compatibility	Windows: ¹⁹ Windows [®] 10, Windows 8.1, Windows 7 SP1 Mac: ²⁰ Mac OS [®] X v10.10.5 – macOS v10.13 (High Sierra) Mobile Operating Systems: ²² iOS [®] , Android [™] , Windows 10 Mobile, and Fire OS (Amazon Fire) devices ²³
Mobile Apps (iOS [®] / Android [™])	Canon PRINT app, ¹ Easy-PhotoPrint Editor app, ⁶ Message In Print app ⁸
Print Longevity ²⁴	ChromaLife100 System Up to 100 Years Album Life, or 30 Years Behind Glass (Light Fastness), or 20 Years Without The Glass (Gas Fastness)
Size and Weight	Closed: 14.7" (L) x 14.4" (W) x 6.3" (H) / 14.4 lbs. Paper Installed: 14.7" (L) x 24.8" (W) x 12.7" (H)
Warranty ²⁵	1-Year limited warranty with InstantExchange Program.

PRODUCT / INK INFORMATION

Model No.	PIXMA TS702	Compact Connected Inkjet Printer	3109C002
Compatible Inks	PGI-280 PGBK XXL	XXL Pigment Black Ink Tank	1967C001
	CLI-281 BK XXL	XXL Black Ink Tank	1983C001
	CLI-281 C XXL	XXL Cyan Ink Tank	1980C001
	CLI-281 M XXL	XXL Magenta Ink Tank	1981C001
	CLI-281 Y XXL	XXL Yellow Ink Tank	1982C001
	PGI-280 PGBK XL	XL Pigment Black Ink Tank	2021C001
	CLI-281 BK XL	XL Black Ink Tank	2037C001
	CLI-281 C XL	XL Cyan Ink Tank	2034C001
	CLI-281 M XL	XL Magenta Ink Tank	2035C001
	CLI-281 Y XL	XL Yellow Ink Tank	2036C001
	PGI-280 PGBK	Pigment Black Ink Tank	2075C001
	CLI-281 BK	Black Ink Tank	2091C001
	CLI-281 C	Cyan Ink Tank	2088C001
	CLI-281 M	Magenta Ink Tank	2089C001
	CLI-281 Y	Yellow Ink Tank	2090C001



FOR MORE INFORMATION VISIT WWW.USA.CANON.COM/CONSUMER

SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE. ALL VIEWSCREEN AND PRINTER OUTPUT IMAGES ARE SIMULATED.

- Requires an Internet connection and the Canon PRINT Inkjet / SELPHY app, available for free on the App Store and at Google Play. Compatible with iPad, iPhone 3GS or later, and iPod touch 3rd generation or later devices running iOS 7.0 or later, and Android mobile devices running Android 2.3.3 or later. Your device must be connected to the same working network with wireless 802.11 b/g/n/ac/ad capability as your printer. Requires a compatible social media account and is subject to that social media account's Terms of Service. Certain exceptions may apply.
- Paper types NOT supported for borderless printing are as follows: Envelope, High Resolution Paper, T-Shirt Transfer and Photo Stickers. The maximum borderless printing size is 8.5" x 11."
- Wireless printing and scanning requires a working network with wireless 802.11b/g/n capability, operating at 2.4GHz. Wireless performance may vary based on terrain and distance between the printer and wireless network clients.
- AirPrint functionality requires a compatible iPad, iPhone, or iPod Touch device running iOS 7.0 or later, and an AirPrint-enabled printer connected to the same network as your iOS device. A printer connected to the USB port of your Mac, PC, AirPort Base station, or Time Capsule is not supported.
- Requires Android mobile device with Android 4.4 operating system or later with the Mopria Print Service pre-loaded with that device and the compatible PIXMA printer on the same wireless network. The Mopria experience is also available on Android 4.4 mobile devices with a download of the Mopria Print Service from Google Play.
- The Easy-PhotoPrint Editor software requires an Internet connection and is compatible with the following operating systems; Microsoft Windows 10 (64-bit/32-bit), Microsoft Windows 8.1 (64-bit/32-bit), Microsoft Windows 7 SP1 (64-bit/32-bit), macOS High Sierra v10.13, macOS Sierra v10.12, Mac OS X El Capitan v10.11 and Mac OS X El Capitan v10.10.5. Minimum Windows and macOS/Mac OS X requirements are: 2GB of RAM and a monitor with 1024x768 resolution. The Easy-PhotoPrint Editor mobile application requires an Internet connection and the Easy-PhotoPrint Editor app v1.1.0, available for free on the App Store and at Google Play. Compatible with iPad Air2 (2nd Generation), iPad Mini 4 and iPhone 6s or later devices running iOS 10 or later, and Android mobile devices running Android 5.x or later. Certain exceptions may apply. The following file formats are supported: JPEG, PNG, HEIF (devices running iOS 11 and mac OS v10.13 or later), DLP save data, Poster Artist export data, EasyPhoto+ export data, Easy-PhotoPrint Editor export data.
- Requires an Internet connection and Google account. Subject to Google Terms of Service. Certain exceptions may apply.
- Requires an Internet connection and the Message In Print app (Version 1.1.), available for free on the App Store and at Google Play. Compatible with iPad and iPhone 6 or later devices running iOS 10 or later, and Android mobile devices running Android 5.1 or later. Your device must be connected to the same working network with wireless 802.11 b/g/n/ac/ad capability as your printer. Requires original content to be created using the Message In Print app/service, then printed on a compatible Canon Printer released in August 2009 or later and delivered to recipient, who views image and content through the compatible Message In Print app on their compatible device. Compatible paper sizes include 3.5" x 3.5", 4" x 4" Square, 4" x 6" and 5" x 5" Square only, and compatible media types include Genuine Canon Photo Paper Glossy, Photo Paper Semi-Gloss, Photo Paper Luster and Photo Paper Matte only. Certain exceptions may apply.
- Document print speeds are the averages of ESAT in Office Category Test for the default simplex mode, ISO/IEC 24734. Photo print speed is based on the default setting using ISO/JIS-SC18 N2 on Photo Paper Plus Glossy II and does not take into account data processing time on host computer. Print speed may vary depending on system configuration, interface, software, document complexity, print mode, page coverage, type of paper used etc. Copy speeds are the average of sFCOT and sESAT, ISO/IEC 29183. Copy speed may vary depending on document complexity, copy mode, page coverage, type of paper used etc. and does not take into account warming up time. See www.usa.canon.com/ipm for additional details.
- Resolution may vary based on printer driver setting. Color ink droplets can be placed with a horizontal pitch of 1/4800 inch at minimum.
- Compatible with iPad, iPhone or iPod touch devices running iOS 9.0 or later, or Android mobile devices running Android 5.1 or later, with Bluetooth hardware enabled. For full print functionality Canon PRINT Inkjet / SELPHY app must be open and paired to use Bluetooth functions, available for free on the App Store and at Google Play. Bluetooth communication and functionality cannot be guaranteed on all Android devices.
- Canon Print Service is a print plug-in for Android smart devices, which enables printing from Android v4.4 - v5.0 devices to many Canon printers via a Wi-Fi network. The plug-in does not work as a standalone app. Available for free at Google Play.
- CREATIVE PARK PREMIUM is a premium content service available exclusively to users only when all of the colors of genuine Canon inks and all of the software that came with the printer are properly installed.
- Requires a smart device with the Canon PRINT Inkjet/SELPHY app installed and connected to the desired active wireless network to complete cableless setup.
- Requires an active smart assistant account linked and accompanying app enabled, the smart device and printer to be actively connected with permission to the Canon Inkjet Cloud Printing Center, and the required action(s), skill(s), or applet(s) available/enabled to the compatible printer. Voice commands can not be displayed as text on Amazon smart devices with screens.
- Requires an active IFTTT account, the printer to be actively connected with permission to the Canon Inkjet Cloud Printing Center, and an IFTTT 'applet' installed/enabled and required active account/service linked to the printer.
- DPS over IP compatible device required.
- Duty Cycle is defined as the maximum number of printed pages for a single peak month.
- Operation can only be guaranteed on a PC with pre-installed Windows 10, Windows 8.1, Windows 7 SP1.
- Internet Connection required during software installation. For full compatibility macOS v10.12.1 or later is recommended.
- PosterArtist Lite software v2.60.00 is compatible with 64/32 bit versions of Microsoft[®] Windows[®] 10, Windows 8.1, Windows 8, Windows 7 and Windows Vista[®] and only compatible with Canon PIXMA (released after July 2015), MAXIFY, imagePROGRAF and iC printers. Minimum computer system requirements: Pentium4 2.4GHz CPU or higher with 1GB RAM, 1024 x 768 pixel display and 5GB of system hard drive space.
- Some functions may not be available with these Operating Systems. Please refer to the manual or website for details.
- Requires "Canon Print Plug-in" available for free from the Amazon Appstore and an Amazon Fire Phone, Amazon Kindle Fire HD6 or HDX7 device or later running Fire OS 4.0 or later.
- Based on accelerated testing by Canon in dark storage under controlled temperature, humidity and gas conditions, simulating storage in an album with plastic sleeves. Canon cannot guarantee the longevity of prints; results may vary depending on printed image, drying time, display / storage conditions, and environmental factors. See www.usa.canon.com/chromalife100 for additional details.
- Warranty programs are subject to certain conditions and restrictions. See www.usa.canon.com/support for details.