

## DisplayPort to VGA Active Adapter Video Converter , DP ver 1.2 (M/F), 6-in. (15.24 cm), 50 pack

MODEL NUMBER: P134-06NVGAV2BP



Active adapter connects a VGA display to the DisplayPort (DP) 1.2 output on your laptop or desktop computer for playing 1080p video.

### Features

**DisplayPort to VGA Converters Connect DP Source to VGA Display** This set includes 50 Tripp Lite P134-06N-VGA-V2 DisplayPort to VGA active adapters. Each adapter connects a VGA monitor, television or projector to the DisplayPort 1.2 output on your PC, Mac, Chromebook, MacBook, Microsoft Surface or other compatible computer or tablet. They feature a male DP connector and a female HD15 connector, allowing you to continue using your existing VGA display and VGA cable to transmit video signals without the expense of a new DP display. They also are backward compatible with pre-1.2 DisplayPort generations.

**Transmit Outstanding 1080p Video for High-Definition Presentations** Ideal for classrooms, lecture halls and anywhere else you may need to connect to a VGA monitor, these DisplayPort to VGA converters support computer video resolutions up to 1920 x 1200 (including 1080p) and HD video resolutions up to 1920 x 1080 (1080p). The active adapters convert both Single-Mode and Dual-Mode (DP++) DisplayPort output. They come recommended for use with graphics cards, such as AMD Eyefinity, that do not output DP++ signals.

**Ready to Use Right Out of the Package** The plug-and-play DP to VGA adapters require no software, drivers or external power, work with both Windows and Mac operating systems, and are compatible with laptops, tablets and other devices equipped with a female DisplayPort. With its small size and built-in cable, the P134-06N-VGA-V2 is recommended for stowing in your laptop bag and carrying to school or the office.

### Highlights

- 50-piece bulk pack of P134-06N-VGA-V2 DisplayPort to VGA video adapters
- Delivers high-definition picture quality at resolutions up to 1920 x 1200 (1080p)
- Active adapter converts Single- and Dual-Mode DP++ output for viewing on VGA display
- Compact unit fits easily into briefcase or laptop bag for instant use anywhere
- Plug-and-play operation with no software required for easy, immediate installation

### Applications

- Connect your newer laptop to an older VGA monitor in a lecture hall or conference room for a video presentation
- Add a secondary monitor to the PC or laptop in your office or home workspace
- Display menus, ads, promos, directions and other digital signage applications

### System Requirements

- Source device with DisplayPort output
- Display device with HD15 input
- Not for use with MST Hubs

### Package Includes

- (50) P134-06N-VGA-V2 DisplayPort to VGA Active Converters (M/F), 6 in.



## Specifications

OVERVIEW	
UPC Code	037332237743
Technology	VGA/SVGA; DisplayPort
VIDEO	
Max Supported Video Resolution	1920 x 1200 @ 60Hz
INPUT	
Product Length (in.)	5.9
Product Length (ft.)	0.49
PHYSICAL	
Color	Black
Cable Outer Diameter (OD)	4.5mm
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Ferrite Core	No
Material of Construction	ABS, PVC
Shipping Dimensions (hwd / in.)	1.00 x 15.00 x 17.50
Shipping Weight (kg)	1.77
Unit Dimensions (hwd / in.)	1.46 x 0.57 x 1.77
Unit Weight (kg)	0.10
Unit Weight (lbs.)	0.22
ENVIRONMENTAL	
Operating Temperature Range	32 to 158 F (0 to 70 C)
Storage Temperature Range	14 to 176 F (-10 to 80 C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	HD15 (FEMALE)
Connector Plating	Gold; Nickel



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Contact Plating	Gold; Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
Displayport Specification	1.2
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>