

MINIATURE MP VIDEO BALUN

0E-VBMINIMP

ALL FORMATS UP TO 8 MEGAPIXEL
SCREW TERMINAL TO BNC



Miniature, single-channel passive video balun enables full motion video transmission over UTP up to 2,000', or 3,000' if used with an active receiver. With passive receiver: Standard resolution: up to 2,000' (600m); HD-TVI 720P/1080P: up to 820'(250m); AHD 720P: up to 1,148' (350m)/ 1080P: up to 650' (200m); HD-CVI 720P: up to 1,000' (300m)/1080P: up to 820' (250m); AHD/HD-CVI/TVI 3MP/4MP/5MP: up to 650'; AHD/HD-CVI/TVI 4K/8MP: up to 328' (100m). No power required. Easy installation with screw clamp terminals and BNC connector. One pair per package.

- SCREW CLAMP TERMINAL TO BNC
- FULL MOTION VIDEO TRANSMISSION
- TRANSMITS OVER UTP, CAT5/5E/6/6A
- UP TO 2,000' (600m), 5MP UP TO 650', 8MP TO 328'
- UP TO 3,000' (900m) IF USED WITH ACTIVE RCVR
- HIGH INTERFERENCE REJECTION
- HIGH TRANSIENT PROTECTION
- NO POWER REQUIRED

PART #: 0E-VBMINIMP

UPC: 840049300392

LENGTH: 0.94"

WIDTH: 0.56"

HEIGHT: 1.25"

WEIGHT: 0.6 OUNCE (EACH)