



## 23.8" FHD 1920 x 1080 ADS-IPS LED Monitor

### L238E-2N

SKU: 5RR310

The sleek 23.8" monitor from V7 is a stunning display and features DVI, HDMI, VGA and DisplayPort inputs. The L238E has HD 1920x1080 resolution, vivid colors and integrated speakers, for a great media experience. It also features an ADS-IPS Panel for a wide viewing angle. Additionally, the display is VESA 100x100mm mountable to free up desk space, making it a smart choice for the home or office.

- 1920 x 1080 Resolution Full HD
- Amazing from any angle – with ADS-IPS panel technology enjoy an extra wide 178°(H) / 178°(V) viewing angle
- Multiple Input options with VGA, DVI, HDMI, & DisplayPort with HDMI Cables included
- 100 x 100 VESA mounting pattern available for easy attachment to desk or wall mounts
- Multiple picture options include Standard, Gaming, Landscape and Text modes

#### General

Sku: 5RR310  
 Model: L238E-2N  
 UPC: 662919103922  
 Warranty: 3 years  
 Compliance: CE, Energy Star, FCC, ICES, ISO 9241-3x  
 Class 2, RoHS, TCO, WEEE  
 Country Of Origin: China  
 Package Type: One Color  
 Package Includes: Monitor with stand and base,  
 Quick installation guide, HDMI Cable, US Power  
 Cord, Warranty Card

#### Color

Color: Black

#### Design

Monitor Feature: Fixed Stand

#### Package Dimensions

Package Dimensions (L/W/H): 60.7 x 12.5 x 41cm  
 Shipping Weight: 7.3 Kg (16 lbs)  
 Package Weight: 7.3 Kg (16 lbs)

#### Product Dimensions

Product Dim (L/W/H): 54.7 x 21 x 40.4cm (21.5 x 8.3  
 x 15.9 in)  
 Product Weight: 5.5 Kg (12.1 lbs)

#### California Prop 65

No warning required

#### Technical

Panel Size: 23.8 in  
 Panel Type: ADS  
 Power Input: AC 100V-240V 50-60Hz  
 Aspect Ratio: 16:9  
 Response Time: 5 ms  
 Viewing Angle: 178°H / 178°V  
 Maximum Resolution: 1920 x 1080  
 Screen Coating: Matte  
 Brightness: 250 nits  
 Color Depth: 16.7 million colors  
 EU/UK Energy Rating: A+  
 Contrast Ratio: 1000:1  
 Input Port: DisplayPort, DVI, HDMI, VGA  
 VESA Mount: 100 x 100 mm  
 Input AC Plug Type: NEMA 5-15P (US)  
 Stand: 22.8 x 21 x 14.6cm (8.9 x 8.3 x 5.7 in)  
 Speaker: 2 x 1.5W  
 Monitor Dim (w/o Stand): 54.7 x 4.5 x 32.1cm (21.5 x  
 1.8 x 12.6 in) LxDxH  
 Horizontal Frequency: 83 KHz  
 Display Area (H x L): 50.2 mm (H) x 299.6 mm (V)