

ThinkVision P44w-10 61D5RAR1US

Product
ThinkVision P44w-10

Region
US

Color
Black

Panel
Vertical Alignment

Display Size
43.4"

View Area
1052.3x328.8 mm

Resolution
3840x1200

Aspect Ratio
32:10

Pixel Pitch
0.2740x0.2740 mm

Dot / Pixel Per Inch
93 dpi

Brightness
380 nits

Contrast Ratio
3000:1

Pixel Response Time
4 ms (extreme mode) / 6 ms(typical)

Color Gamut
99.5%

View Angle (H / V)
178 / 178

Stand
Tilt, Swivel, Height Adjust Stand

Side Bezel Width
2.4 mm

Dimensions with Stand (HxWxD)
591.1x1058.3x269.8 mm

Power Consumption (Typical / Maximum)
70W / 250W

Power Adapter
Integrated

Weight (Including Stand)
29.65lb / 13.45kg

Warranty
3-year

ENERGY STAR
ENERGY STAR 7.1

TCO
TCO 8.0

EPEAT
No

Presets / User Settings
26 / 26

On Screen Display
OSD, 8 Languages

USB Port
USB 3.1 Gen1 x4, USB 3.1 Type-C Gen 1 x1, USB 3.1 Type-C Gen 2 x1

Speaker
None

Camera
None

Multiple Input
HDMI, DP, USB 3.1 Type-C Gen 1, USB 3.1 Type-C Gen 2

Monitor Cable
HDMI, DP, USB Type-C

CPU / Platform
None / None

Display Ram / Storage / Card Slot
None / None / None

Wireless / Ethernet / Bluetooth
None / None / None

Touch Screen / Digitizer Pen / Battery
None / None / None

Operating System
Support Windows 7, Windows 10

Ann Date (mm/yy)
02/19

Notes:

California Electronic Waste Recycling Fee

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:

<https://www.calrecycle.ca.gov/Electronics/Consumer>



WWW.LENOVO.COM

This publication was developed for products and services offered in the United States and E.M.E.A countries. Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication “as is” without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2019. All rights reserved.



Lenovo™

ThinkVision P44w-10

Specifications

DISPLAY

Panel Size

43.4 inches

Screen Dimensions (H x V)

1052.3 x 328.8mm
41.4 x 12.9 inches

Panel Type

VA NearEdgeless,
anti-glare

Curvature

1800R

Backlight

WLED

Aspect Ratio

32:10

Resolution

3840 x 1200

HDR

VESA Certified DisplayHDR™ 400

Pixel Pitch (H x V)

0.2740 x 0.2740mm

Viewing Angle (H x V)

178°/178°

Response Time (gray to gray)

4/6ms (extreme/typical)

Refresh Rate

Max. 144Hz

Contrast Ratio (typical)

3000:1

Dynamic Contrast Ratio (typical)

3M:1

Color Support (typical)

1.07B

Color Gamut

sRGB: 99.5%
BT.709: 99.5%
DCI-P3: 90%

Brightness

380 nits (typical)
450 nits (peak)

CONNECTIVITY

Video Input Signals

2 x HDMI 2.0
1 x DP1.4
1 x USB Type-C Gen1 (DP1.2 Alt Mode)
1 x USB Type-C Gen2 (DP1.4 Alt Mode)

Video Cable Length

1.5m for USB Type-C Gen2
1.8m for others

Audio Out

Yes (3.5mm)

USB Hub

Yes

USB Upstream

2 x USB 3.1 (1 x USB Type-C Gen1,

1 x USB Type-C Gen2)

USB Downstream

4 x USB 3.1 Gen1 (1 BC)

Power

Internal

Power Consumption

Typical/Max: 70W/250W
Switch-off Mode: <0.5W
Sleep/Off Mode: <0.5W

DIMENSIONS

Size Packed (D x H x W)

1219 x 500 x 376mm
47.99 x 19.68 x 14.80 inches

Size Unpacked w/stand (D x H x W) (Lowest Position)

269.8 x 461.1 x 1058.3mm
10.62 x 18.15 x 41.67 inches

Size Unpacked w/stand (D x H x W) (Highest Position)

269.8 x 591.1 x 1058.3mm
10.62 x 23.27 x 41.67 inches

Size Unpacked w/o stand (D x H x W) (Head Only)

137.2 x 366.1 x 1058.3mm
5.40 x 14.21 x 41.67 inches

Weight Packed

18.59kg/40.98lbs.

Weight Unpacked

13.45kg/29.65lbs.

Weight (Monitor Head Only)

9.35kg/20.61lbs.

SPECIAL FEATURES

Anti-Glare

Yes

PIP/PBP

Yes

Software

Yes (ThinkColor)

Speaker

Supports optional Harman
Kardon certified speaker

MECHANICAL

Tilt Angle (front/back)

-5°/22°

Swivel Angle (left/right)

±30°

Lift (Max. range)

Yes (130mm)

VESA Mount Capability

Yes (100 x 100mm)

Kensington™ Lock Slot

Yes

Cable Management

Yes

Bezel Color

Raven Black

Bezel Width (side)

2.4mm

Bezel Width (top/bottom)

2.4/25.6mm

WHAT'S IN THE BOX

Monitor with stand
1 x Power cable
1 x HDMI cable
1 x DP cable
1 x USB Type-C Gen2 cable
1 x USB Type-C to Type-A cable
Quick setup guide

CERTIFICATIONS

ENERGY STAR® Rating

71

CCC

Yes

RoHS

Yes

ULE

Gold

TCO

8.0

Windows Certification

Windows 7, Windows 10

China Energy Efficiency Standard

Tier 2

Ambient Operating Temperature

0°C to 45°C

TÜV Eye Comfort

Yes



*with FreeSync support graphic cards

© 2019 Lenovo. All rights reserved. Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: 5 Gbit/s for USB 3.1 Gen1, 10 Gbit/s for USB 3.1 Gen2 & 20 Gbit/s for USB 3.2. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

ThinkVision P44w-10

