

4K HDMI Fiber Active Optical Cable (AOC) - 4K 60 Hz, HDR, 4:4:4 (M/M), 15 m

MODEL NUMBER: P568-15M-FBR



Fiber HDMI cable creates crystal-clear Ultra HD 4K x 2K video/audio connections with 4:4:4 color for home theaters and digital signage.

Features

4K HDMI Cable Connects Home Theater, Gaming & Digital Signage Components

This 4K HDMI cable securely connects HDMI-enabled laptops, tablets, PCs, Blu-ray players, game consoles or satellite/cable TV boxes to HDTVs, HD monitors, projectors or home theater receivers. Because the cable uses optical fiber, it can transmit HDMI signals longer distances with no latency or loss. It also eliminates any EMI/RFI line noise that can interfere with your audio/video signal and disrupt the performance of your connected equipment.

Enjoy the Clarity of 4K HDMI Video with Multi-Channel Audio, HDR and 4:4:4 Color

This 4K HDMI cable is rated up to 18 Gbps and supports Ultra HD video resolutions up to 4K at 60 Hz (3840 x 2160) for crystal-clear picture and sound, as specified in HDMI 2.0. High Dynamic Range (HDR) provides a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 4K display. It also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor, as well as 3D, 48-bit Deep Color, DTS-HD Master Audio and Dolby True HD.

Advanced Fiber Cable Is Easier to Install than Copper

Because the fiber cable is slimmer and more flexible than standard copper HDMI cables, the P568-15M-FBR is easier to install around corners and in hard-to-reach spaces behind equipment. It draws power from the connected device, so no external power supply is needed to transmit the HDMI signal across the longer distances unique to fiber optic cabling. **Note:** *The cable must be installed in the correct direction to function properly, so check the Source and Display labels on the connectors before installation.*

Highlights

- Supports UHD resolutions up to 4K @ 60 Hz (4:4:4) for crystal-clear video
- Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy
- Fiber optic strands transmit audio/video over longer distances than standard copper
- Dispels EMI/RFI line noise that can disrupt A/V signal and affect equipment performance
- Plug-and-play cable draws power from connected device for easy, immediate installation

Applications

- Watch 4K video content from a Blu-ray player, game console, laptop or tablet on an Ultra HD television, monitor or projector
- Connect a Chromebook or MacBook to a conference table's A/V box to give a video presentation on a large screen
- Send Ultra HD content to digital signs or point-of-sale displays
- Connect security cameras and other A/V surveillance equipment to a central display

Package Includes

- P568-15M-FBR High-Speed HDMI Fiber Active Optical Cable, M/M, Black, 15 m (50 ft.)

Specifications



OVERVIEW	
UPC Code	037332236821
Product Type	Active Optical Cable (AOC)
Technology	HDMI; HDR
VIDEO	
Video Input	HDMI (MALE)
Video Output	HDMI (MALE)
Max Supported Video Resolution	3840x2160 (4K @ 60Hz)
Max 1280 x 720 (720p) Range (ft)	49
Max 1920 x 1080 (1080p) Range (ft)	49
Max 1920 x 1200 Range (ft)	49
Max 2560 x 1600 Range (ft)	49
Max 3840 x 2160 (4K@30Hz) Range (ft)	49
Max 3840 x 2160 (4K@60Hz) Range (ft)	49
Signal Range (ft)	49
Signal Range (m)	15
Max Supported Color Depth	48-bit
HDR Support	Yes
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
PHYSICAL	
Color	Black
Cable Length (ft.)	50
Cable Length (m)	15
Number of Displays	1
Form Factor/Mounting Options	Cable
Shipping Dimensions (hwd / cm)	5.08 x 18.80 x 20.32
Shipping Dimensions (hwd / in.)	2.00 x 7.40 x 8.00
Shipping Weight (kg)	0.61
Shipping Weight (lbs.)	1.34
ENVIRONMENTAL	
Operating Temperature Range	32 to 113°F (0 to 45°C)



Storage Temperature Range	14 to 158°F (-10 to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
COMMUNICATIONS	
USB Extension Support	No
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
FEATURES & SPECIFICATIONS	
Driver Required	No
Built-In Equalizer	No
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>