

6ft (2m) Durable USB A to Lightning Cable - Black 90 Right Angled Heavy Duty Rugged Aramid Fiber USB Type A to Lightning Charging/Sync Cord - Apple MFi Certified - iPhone

**Product ID:** RUSBLTMM2MBR



This angled Lightning to USB cable withstands the demands of charging and syncing your mobile devices. The angled Lightning connector gives you easy access to your mobile device, even while charging. And, and the longer cable is ideal for overcoming distance restrictions.

With aramid fiber reinforcement, the durable Lightning cable is sheltered from the stress of frequent bends and twists, which allows the cable to flex without over-stretching.

<ol>

- Aramid fiber adds strength and durability to the cable
- Insulated conductors reduce friction, provide more flexibility
- EMI (electromagnetic interference) protection with aluminum-mylar foil and braided shielding
- TPE (thermoplastic elastomer) cable jacket is softer and more flexible than a standard PVC cable</ol>

Constructed to prevent the connector from separating from the cable jacket, the extra-long strain relief molding is tested to withstand over 10,000+ bend cycles at a 180 angle.<ol>

- Lightning connector provides 12W for charging your iOS devices
- Metal shield protects circuit board from EMI and reinforces the connection point
- Strain relief tested to tolerate over 10,000+ bend cycles at a 180-degree angle </ol>

RUSBLTMM2MBR is an Apple MFi certified Lightning cable backed by a StarTech.com 2-year warranty.

## Certifications, Reports and Compatibility



## Applications

- Charge and sync your Lightning mobile devices
- Text, work, or game without the cable getting in the way
- Easy access in both portrait and landscape mode

## Features

- **DURABLE:** 6.5 ft. Heavy duty lightning cable w/aramid fiber for high tensile strength increasing reliability & cable life; long lasting tested to withstand 10000+ bend cycles at 180 angle & 5000+ insertions
- **FLEXIBLE CABLE:** Built w/TPE jacket to absorb the stress of frequent bends while protecting the cable core. Durable wire & connector shields rugged charging cord from wear & tear of frequent in-car use
- **RIGHT ANGLED CONNECTOR:** 90 degree connector eliminates tension & protects the lightning port of iPhone 12 Pro/Max/Mini, iPhone 8/11/11 Pro, iPhone XR, iPad Air, iPad, iPad Mini. Ideal for car mounts, classroom desk mounts or mounted POS
- **APPLE MFI CERTIFIED:** Fast & reliable charge from USB-A charger/port to lightning devices, including AirPods, Magic Keyboard, Magic Trackpad, Magic Mouse. Supports USB 2.0 480 Mbps data transfers
- **CABLE SPECS:** Length: 2 m (6.5 ft.) Color: Black Connectors: Angled Lightning to USB-A Performance: USB 2.0 Reinforcement: Aramid Fiber Jacket Type: TPE Shielding: Al-Mylar Backed by StarTech.com for 2 years

---

### Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

### Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

---

### Connector(s)

Connector A	1 - USB Type-A (4 pin) USB 2.0
-------------	--------------------------------

Connector B 1 - Apple Lightning Connector (8-pin)

---

**Physical Characteristics**

Color	Black
Connector Style	Angled
Wire Gauge	22/32 AWG
Cable Length	6.6 ft [2 m]
Product Length	6.6 ft [2.0 m]
Product Width	1.0 in [26.1 mm]
Product Height	0.3 in [0.7 cm]
Weight of Product	1.6 oz [45.0 g]

---

**Packaging Information**

Package Length	6.3 in [16.0 cm]
Package Width	3.0 in [75.0 mm]
Package Height	1.2 in [30.0 mm]
Shipping (Package) Weight	0.2 lb [0.1 kg]

---

**What's in the Box**

Included in Package	1 - 2 m Lightning Cable
---------------------	-------------------------

---

***\*Product appearance and specifications are subject to change without notice.***

