

ThinkVision T27p-10 61DAMAR1US

Product

ThinkVision T27p-10

Region

US

Color

Black

Panel

In-Plane Switching

Display Size

27"

View Area

596.73x335.66 mm

Resolution

3840x2160

Aspect Ratio

16:9

Pixel Pitch

0.1554x0.1554 mm

Dot / Pixel Per Inch

163 dpi

Brightness

350 nits

Contrast Ratio

1000:1

Pixel Response Time

4 ms (extreme mode) / 6 ms/14 ms (typical/off mode)

Color Gamut

99%

View Angle (H / V)

178 / 178

Stand

Tilt Stand

Side Bezel Width

2 mm

Dimensions with Stand (HxWxD)

403.3x611.6x210.0 mm

Power Consumption (Typical / Maximum)

50W / 140W

Power Adapter

Intergrated

Weight (Including Stand)

15.32 lb / 6.95kg

Warranty

3-year

ENERGY STAR

ENERGY STAR 7.1

TCO

TCO 8.0

EPEAT

Silver

Presets / User Settings

22 / 20

On Screen Display

OSD, 8 Languages

USB Port

USB 3.1 Gen1 x 4, USB 3.1 Type-C Gen 1 x1

Speaker

None

Camera

None

Multiple Input

HDMI, DP, USB 3.1 Type-C Gen 1

Monitor Cable

HDMI, USB Type-C

CPU / Platform

None / None

Display Ram / Storage / Card Slot

None / None / None

Wireless / Ethernet / Bluetooth

None / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

Operating System

Support Windows 7, Windows 10

Ann Date (mm/yy)

05/19

Notes:

California Electronic Waste Recycling Fee

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>



WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2019. All rights reserved.



ThinkVision T27p-10



DISPLAY	POWER	Audio Out	MECHANICAL	CERTIFICATIONS
Panel Size 27.0 inches	Power Consumption (Typical/Max) 50W/140W	Yes (3.5mm)	Tilt Angle (front/back) -5°/30°	ENERGY STAR® Rating 7.1
Screen Dimensions (H x V) 596.74 x 335.66mm	Power Consumption Sleep/Off Mode <0.5W	DIMENSIONS	Swivel Angle (left/right) +/-45°	EU RoHS Yes
Panel Type In-Plane Switching	Power Consumption Switch Off-Mode <0.3W	Size Packed (D x H x W) 732 x 210 x 453mm/ 28.82 x 8.27 x 17.83 inches	Lift Yes (110mm)	CCC Yes
Backlight WLED	Power Supply Internal	Size Unpacked w/stand (D x H x W) (mm/inch) (Head Only) 269.8 x 403.3 x 611.6mm/ 10.62 x 15.88 x 24.08 inches	Pivot +/-90°	Windows Certification Windows 7, Windows 10
Aspect Ratio 16:9	ENERGY STAR® (P_{on}) 23.40W	Size Unpacked w/o stand (D x H x W) (mm/inch) (Head Only) 45.5 x 368.4 x 611.6mm/ 1.79 x 14.5 x 24.08 inches	VESA Mount Capability Yes (100 x 100mm)	China Energy Efficiency Standard Tier 2
Resolution 3840 x 2160 pixels	ENERGY STAR® (E_{TEC}) 101.94kWh	Weight Packed 11.00kg/24.25lbs.	Kensington™ Lock Slot Yes	TÜV Eye Comfort Yes
Pixel Pitch (H x V) 0.1554 x 0.1554mm	Voltage Required 100-240VAC (50/60Hz)	Weight Unpacked 6.95kg/15.32lbs.	Bezel Width (Side) 2.0mm	TCO TCO 8.0/TCO Edge 2.0
Viewing Angle (H x V) 178°/178°	CONNECTIVITY	Weight (Monitor Head Only) 5.0kg/11.02lbs.	Bezel Width (top/bottom) 2.0/24.5mm	ULE Gold
Response Time (gray to gray) 4ms (extreme mode) 6ms (normal mode)	Video Input Signals HDMI 2.0 + DP 1.2 + USB 3.1 Type-C™ (DP 1.2 Alt Mode)	SPECIAL FEATURES	WHAT'S IN THE BOX	
Refresh Rate 60Hz	Video Cables Supplied USB 3.1 Type-C™ + HDMI	Smart Power* Yes	Monitor with stand 1 x Power Cable 1 x HDMI Cable 1 x USB Type-C™ to Type-C™ cable Quick Setup Guide	
Contrast Ratio (typical) 1000:1	Video Cable Length 1.8m	Anti-glare Yes		
Dynamic Contrast Ratio (typical) 3M:1	USB Hub Yes	ThinkCentre Tiny Support Yes		
Brightness (typical) 350 cd/m ²	USB Upstream 1 x USB 3.1 Gen1 (by USB Type-C™)	Optional Soundbar Support Yes		
Color Gamut sRGB (CIE 1931) 99%	USB Downstream 4 x USB 3.1 Gen1 (with 1 BC)			
Color Support 1.07 Billion				

*The Smart Power function intelligently detects overall power consumption and dynamically manages the power delivery to each device. 75W power delivery can be achieved when downstream USB ports are not connected and OSD brightness setting is <61.

Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: - 5 Gbit/s for USB 3.1 Gen1; 10 Gbit/s for USB 3.1 Gen2 & 20 Gbit/s for USB 3.2.

© 2019 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.



ThinkVision T27p-10

Lenovo

