

# Business Laser Printer

HL-L6400DWX



**The HL-L6400DWX monochrome laser printer is ideal for mid to large-sized workgroups with high print volumes, looking for a low total cost of ownership, advanced security features, and improved productivity.**

- Help maximize your budget with included 20,000 page<sup>▼</sup> Brother Genuine ultra high-yield cartridge
- Includes value added services for optimizing document workflow, enhancing security, and managing fleet environments\*\*
- Triple layer security features help limit device and document access and help protect from network intrusion
- Large standard paper capacity helps minimize user intervention and scalable paper handling is ideal for workgroups that require customized workflows
- Help improve your document workflow with a fast print speed
- Color Touchscreen for easy navigation and direct printing from popular business cloud services<sup>▲</sup>
- Flexible installation options for easily sharing the printer on your wireless or Gigabit Ethernet network and mobile device<sup>□</sup>

# HL-L6400DWX

## Specifications:

Print Technology	Electrophotographic Laser
LCD Display (type/size)	1.8" Color Touchscreen Display
Paper Size (maximum)	Paper Trays: Up to 8.5" x 14" (legal) Multi-Purpose Tray: 3.0" - 8.5" (W) / 5.0"-14" (L)
Print Speed (maximum)**	Up to 52ppm
Time to First Page <sup>▲</sup>	Less than 7.5 seconds
Print Resolution (maximum)	Up to 1200 x 1200 dpi
Processor	800 MHz
Emulations	PCL5e, PCL5c, PCL6 (PCL XL Class 3.0), BR-Script3*, IBM Proprinter, Epson FX, PDF version 1.7
Duplex Printing Capability	Yes (default setting)
Paper Input Capacity (maximum) <sup>Ⓞ</sup>	520-sheet capacity paper tray, 50-sheet capacity multi-purpose tray
Optional Input Capacity (max.*) <sup>Ⓞ</sup>	2,650 sheets via optional tower tray
Output Capacity (std. / max.*) <sup>Ⓞ</sup>	250 sheets (face down), 10 sheets (face up), 1,050 sheets via optional mailbox
Media Types	Plain Paper, Letterhead, Colored Paper, Recycled Paper, Bond, Labels, Envelopes (up to 10)
Media Weights	Standard Paper Trays: 16 to 32 lbs. Multi-Purpose Tray: 16 to 53 lbs.
Memory (std. / max.)	512MB / 512MB
Standard Interfaces	Wireless 802.11b/g/n, NFC+, Gigabit Ethernet, USB 2.0
USB Host	Yes, Back (for external IC Card Reader) <sup>Ⓞ</sup>
Operating Systems Compatibility	Windows XP Home, XP Professional, XP Professional x64 Edition, Vista, 7, 8, 8.1, 10; Server 2003, 2003 R2 (32/64 bit), 2008, 2008 R2, 2012, 2012 R2, 2016, 2019 macOS <sup>®</sup> v10.8.5, 10.9.x, 10.10.x, 10.11.x, 10.12.x, 10.13.x, 10.14.x, 10.15.x Linux
Mobile Device Compatibility <sup>□</sup>	AirPrint <sup>®</sup> , Brother iPrint&Scan, Mopria <sup>®</sup> , Wi-Fi Direct <sup>®</sup> , NFC <sup>+</sup>
Web Connect <sup>▲</sup>	GOOGLE DRIVE™, ONEDRIVE, DROPBOX, BOX, ONENOTE, EVERNOTE <sup>®</sup>
Security Features	Integrated NFC Card Reader, Active Directory, Secure Function Lock, Enterprise Security (802.1x), Lock Slot, Secure Print, SSL/TLS, IPsec
Warranty	1-year limited warranty

\*\* Based on one-sided printing. Change from default setting required.

▲ From ready mode and standard tray.

□ PostScript<sup>®</sup>3™ compatible.

Ⓞ Maximum capacity based on using 20 lb. paper.

\* Additional purchase required.

Ⓞ Requires connection to a wireless network.

▼ Approximate toner cartridge yield in accordance with ISO/IEC 19752 (letter/A4).

▲ Approximately 50,000 pages based on 3 pages per job and 30,000 pages based on 1 page per job and [letter/A4 simplex pages]. The number of pages may be affected due to a variety of factors including but not limited to media type and media size.

▲ Requires an Internet connection and an account with desired service.

+ The mobile device must have NFC capability and run Android OS 4.0 or later.

Ⓞ See [www.brother.com](http://www.brother.com) for details.

\*\* Included Brother value services require activation.

## Supplies & Accessories\*:

TN-820	Standard Yield Toner Cartridge (approx. 3,000 pages) <sup>▼</sup>
TN-850	High-Yield Toner Cartridge (approx. 8,000 pages) <sup>▼</sup>
TN-880	Super High-Yield Toner Cartridge (approx. 12,000 pages) <sup>▼</sup>
TN-890	Ultra High-Yield Toner Cartridge (approx. 20,000 pages) <sup>▼</sup>
DR-890	Drum Unit (approx. 50,000 pages) <sup>▲</sup>
LT-5505	Optional 250-Sheet Capacity Paper Tray
LT-6505	Optional 520-Sheet Capacity Paper Tray
TT-4000	Tower Tray with Stabilizer
MX-4000	4-Bin Mailbox/Stacker/Sorter
CB-2000	15.7" Printer Cabinet/Stand
CH-1000	Card Reader Holder

## Included Value Added Services\*\*:

- Custom UI
- Secure Print +
- Barcode Print +
- E-Notify
- Remote Panel
- ThinPrint Client
- Infrastructure Optimization Assessment



At your side support. Online, call or live chat – free support for the life of your printer. At Brother, we want to ensure that your experience with us is exceptional. Visit us at [brother-usa.com](http://brother-usa.com) where you can download the latest product drivers and software, view product manuals, learn how to get the most out of your product with how-to videos and find answers to frequently asked questions.



### Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth. [www.brotherearth.com](http://www.brotherearth.com)

COMPATIBLE WITH  
**WINDOWS**

