## **LG IT MONITORS**



## 27UL550-W.AUS

27" Class 4K UHD IPS LED HDR Monitor with Ergonomic Stand (27" Diagonal)

27" UHD (3840 x 2160) IPS Display sRGB 98% Color Gamut **HDR 10** Height / Pivot / Tilt Adjustable Stand Radeon FreeSync™ Technology **OnScreen Control** 



PICTURE QUALITY	
Screen Size	27" Flat
Panel Type	IPS
Color Gamut (Typ.)	sRGB 98% (CIE1931)
Color Depth(Number of Colors)	1.07B
Pixel Pitch(mm)	0.1554 x 0.1554 mm
Response Time (GTG)	5ms (GtG at Faster)
Refresh Rate	60Hz
Aspect Ratio	16:9
Resolution	3840 x 2160
Brightness	300cd (typ) / 240cd (Min)
Contrast Ratio	700:1 (Min.), 1000:1 (Typ.)
Viewing Angle	178°(R/L), 178°(U/D)
Surface Treatment	Anti Glare, 3H
INPUT/OUTPUT	
HDMI	Yes x 2
DisplayPort	Yes x 1
Headphone Out	Yes

POWER	
Туре	Adapter
Input	100-240Vac, 50/60Hz
Power Save/Sleep Mode (Max)	< 0.5W
DC Off (Max)	< 0.3W
Power Consumption (Typ.)	36W
Power Consumption (Energy Star)	26W
Power Consumption (Max.)	41W
SPECIAL FEATURES	
Color Weakness	Yes
Adaptive Sync	RADEON FreeSync™
Black Stabilizer	Yes
Dynamic Action Sync	Yes
Flicker Safe	Yes
Smart Energy Saving	Yes
Reader Mode	Yes
Super Resolution +	Yes
Color Calibrated	Yes
Dual controller	Yes
On Screen Control (OSC)	Yes
HDR (High Dynamic Range)	HDR10
HDR Effect	Yes
SOUND	
Speaker	No built-in speaker

DIMENSIONS / WEIGHTS	
With Stand (WxHxD)	24.5" x 22.5" x 9.1" (Up) 24.5" x 18.2" x 9.1" (Down)
Without Stand (WxHxD)	24.5" x 14.6" x 1.8"
Shipping Dimensions (WxHxD)	27.7" x 20.4" x 7.6"
With Stand Weight	13.2 lbs
Without Stand Weight	9.7 lbs
Shipping Weight	19.0 lbs
STAND	
Display Position Adjustments	Height/Pivot/Tilt
CABINET / ACCESSORIES	
Wall Mount Size (mm)	100 x 100 mm
Display Port	Yes
HDMI	Yes
STANDARD	
UL(cUL)	Yes
FCC-B	Yes
Power Cord	Yes
WARRANTY	
Limited Warranty	1 Year Parts and Labor
UPC	719192629820