

Cubicle Monitor Mount - Cubicle Wall Single Monitor Hanger - Up to 34" VESA Mount Display - Height Adjustable Ergonomic Office Cubicle Hanging Flat Panel Hook & Clamp Bracket

Product ID: ARMCBCLB



Free up valuable desk space in your cubicle workstation with this cubicle monitor mount. It lets you mount a monitor on your cubicle wall to keep your work area more organized, comfortable and productive.

Heavy-Duty Steel

The cubicle monitor hanger, made of steel with a metallic silver finish, securely supports a 17" to 34" VESA mount monitor, with a maximum weight of 17.6 lb. (8 kg).

Free Up Desk Space

The cubicle wall monitor mount helps you free up surface area in your workspace, and keeps cables neat with integrated cable management.

Adjustable for Ideal Viewing

Adjust your screen height quickly, by pulling the lever while sliding the monitor to the desired height. Up to 12" of height adjustment accommodates a wide range of users.

For customized viewing, tilt your monitor +/-10 degrees and swivel +/-10 degrees. The cubicle monitor mount also rotates +/-180 degrees, for landscape or portrait positioning.

Scalable Solution

Customize your work area by hanging multiple monitors, using several cubicle monitor hangers to create a multi-monitor workstation. The micro-adjustment feature lets you align your monitors in perfect unison. Plus, angle your monitors for optimum viewing.

Virtually No Assembly

The cubicle-wall monitor mount is easy to set up. The monitor mount works in most cubicles, with wall sizes from 1.5" to 3.5" in thickness. It's optimized for wall heights ranging from 19" to 30" above the desk surface.

ARMCBLB is backed by a StarTech.com 5-year warranty and free, lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Maximize desk space in cubicle-style work environments
- Rotate the monitors to portrait orientation, ideal for web design and coding
- Hang multiple monitors over a cubicle wall to create a multi-monitor workstation

Features

- 34" CUBICLE MONITOR MOUNT: VESA 75x75mm/100x100mm compatible single monitor cubicle wall hanger supports displays up to 34 inch (17.6lb/8kg); Silver powder coated finish; 3" profile from cubicle wall
- EASY MONITOR HEIGHT ADJUSTMENT: Total height adjustment range of 12.3" from the top of the office cubicle; Easy-to-use height adjustment hand lever for toolless adjustability across 9 preset levels
- DISPLAY RANGE OF MOTION: Ergonomic hanging cubicle monitor bracket increases comfort & productivity with +/-10° tilt & swivel, 360° screen rotation (landscape/portrait); Tension adjustments tools incl
- EASE OF INSTALLATION: Features quick release detachable VESA plate; Mounting hardware incl. for compatibility; Adjustable clamp supports cubicle wall thickness ranging from 2.5" (63mm) to 3.5" (89mm)
- SCALABLE SOLUTION: Create multi-monitor computer workstations by using several cubicle monitor hangers; Micro-adjustment allows for precise flat panel alignment; Cable management for organized setup

Hardware	Warranty	5 Years
	# of Displays Supported	1
	Articulating	No
	Mounting Options	Cubicle Wall
	VESA Hole Pattern(s)	75x75 mm 100x100 mm
	Wallmountable	No
Performance	Display Rotation	+180° / -180°
	Display Tilt	+10° / -10°
	Fits Curved Display	Yes
	Fits UltraWide Displays	Yes
	Maximum Display Size	34"
	Mounting Surface Thickness	1.5" (38 mm) to 5.5" (139 mm)
	Swivel / Pivot	+10° / -10°
	Weight Capacity (Per Display)	17.7 lb [8 kg]
Physical Characteristics	Color	Silver
	Material	Steel and Plastic
	Product Height	460.500
	Product Length	3.7 in [9.3 cm]
	Product Width	120.000
	Weight of Product	1500.000
Packaging Information	Package Height	140.000
	Package Length	510.000
	Package Width	155.000
	Shipping (Package) Weight	4.3 lb [1.9 kg]
What's in the Box	Included in Package	1 - Cubicle Mount 1 - EVA Foam Pad 1 - Hex Key 4 - Washers 4 - Spacers

4 - M4x12 mm Screws

4 - M4x16 mm Screws

4 - M5x12 mm Screws

4 - M5x16 mm Screws

1 - User Manual

Product appearance and specifications are subject to change without notice.