

28LM520S-WU.AUS

28" HD Smart TV Monitor

28" Wide Viewing Angle Smart TV

Cozy Concept Design

5W x 2 Built-in Speaker

Wall Mountable

Remote Control



PICTURE QUALITY

Size (Inch / cm)	27.5"/70cm
Panel Type	Wide Viewing Angle
Color Gamut (CIE1931)	68%
Color Bit	8bit (6bit+FRC)
Color Depth (Number of Colors)	16.7M
Pixel Pitch(mm)	0.44475x0.44925
Refresh Rate	75Hz
Aspect Ratio	16:9
Resolution	1366x768
Brightness (Typ.)	250 (Typ.), 160(Min.)
Contrast Ratio (Original)	1000:1(typ.)
Contrast Ratio (DFC)	5M:1
Response Time_Typ. (GTG)	8ms
Viewing Angle(CR≥10)	178/178(CR≥10)
Surface Treatment (Glare/non Glare)	non Glare (Haze 1%)

INPUT/OUTPUT

Composite	Yes (commonly used with component)
Component	Yes (commonly used with composite)
HDMI (Ver.)	Yes (HDMI1.4 2EA)
USB (Ver.)	Yes (USB2.0 1EA)
Jack Location	Rear/Side (USB IN)
RCA	Yes
Jack Location	Rear
Optical Out	Yes
Jack Location	Rear
Digital	Yes(ATSC)
Analog	NTSC
Jack Location	Rear
LAN	Yes
Wi-Fi	Yes
Jack Location	Rear

SPEAKER

Type	Internal
Audio output	5W x 2

POWER

Type (w/ Watt)	Adapter (48W)
Input	100-240V
Normal On(Typ.)	30W

FREQUENCY

H-Frequency	30kHz-83kHz
V-Frequency	56Hz-62Hz

CONTROL KEY

Key Number (Power Key Included)	1 key
Key Type	Tact
LED Color(On mode)	Off
LED Color(Standby)	Red
Key Location	Bottom(center)

OSD

Country	36 Country
Number of Language	35 Language (Bosnian, Czech, Danish, German, Estonian, English, Spanish, Greek, French, Gaeilge, Croatian, Italian, Kazakh, Latvian, Lithuanian, Hungarian, Macedonian, Dutch, Norwegian, Uzbekistan, Polish, Portuguese, Russian, Romanian, Albanian, Slovak, Slovenian, Serbian, Finnish, Swedish, Turkish, Ukrainian, Bulgarian, Mongolian, Arabic)
SPECIAL FEATURES	
HDCP	Yes
Remote Control	Yes
Key Lock	Yes
Plug & Play	DDC2B
EPG	Yes
Teletext	Yes
Audio Description (Visual Impaired)	Yes
Flicker Safe	Yes
Reader Mode	Yes
Gaming Mode	Yes (Black Stabilizer)
Cinema Mode	Yes
Divx HD player (USB Media Player)	Yes
USB AutoRun	Yes (Video, Music, Picture)
VoiceOn (Audio Guidance)	Yes
Smart Energy Saving	Yes

Motion Eye Care

Yes
Yes
Yes
Vivid/ Standard/ Eco/ Cinema/ Sports/Game/Expert1/Expert2
Yes

Triple XD engine

Yes
16:9, 4:3
16:9 - DTV, ATV, HDMI
Original - DTV, ATV, HDMI
Full Wide - DTV, ATV
4:3 - DTV, ATV, HDMI
Just Scan - DTV, HDMI (720p1)
All-Direction Zoom - DTV, ATV, HDMI
Vertical Zoom - DTV, ATV, HDMI

ARC-PC

16:9 - DTV, ATV, HDMI
Original - DTV, ATV, HDMI
Full Wide - DTV, ATV
4:3 - DTV, ATV, HDMI
Just Scan - DTV, HDMI (720p1)
All-Direction Zoom - DTV, ATV, HDMI
Vertical Zoom - DTV, ATV, HDMI

ARC-Video

16:9 - DTV, ATV, HDMI
Original - DTV, ATV, HDMI
Full Wide - DTV, ATV
4:3 - DTV, ATV, HDMI
Just Scan - DTV, HDMI (720p1)
All-Direction Zoom - DTV, ATV, HDMI
Vertical Zoom - DTV, ATV, HDMI

Virtual surround

Yes

AVL (Auto Volume)

Yes

Equalizer

Yes

Auto / Manual Clock

Yes

On/ Off Time

Yes

Sleep Timer

Yes

Auto Off / Auto Sleep

Yes

Hotel Mode

Yes

USB Cloning

Yes

DIMENSIONS / WEIGHTS

With Stand (WxHxD)	25.6" x 16.5" x 5.9"
Without Stand (WxHxD)	25.6" x 15.5" x 2.4"
Shipping Dimensions (WxHxD)	28.0" x 17.5" x 4.6"
With Stand Weight	10.0 lbs
Without Stand Weight	9.9 lbs
Shipping Weight	14.3 lbs

STAND

Base Detachable	Yes
Stand Packing Type	Base Detach
Box Printing Type	Flexo 1 color
Remote Controller	Yes
STANDARD	

UL(cUL)	Yes
FCC-B	Yes
Power Cord	Yes
WARRANTY	

Limited Warranty	1 Year Parts and Labor
UPC	719192625969