

Brocade 10G-SFPP-BXU-40K Compatible SFP+ Module - 10GBASE-BX-U - 10 GbE Gigabit Ethernet BiDi Fiber (SMF) (10G-SFPP-BXU-40K-ST)

Product ID: 10G-SFPP-BXU-40K-ST



The 10G-SFPP-BXU-40K-ST is a Brocade 10G-SFPP-BXU-40K compatible upstream fiber SFP transceiver which pairs with StarTech.com's 10G-SFPP-BXD-40K-ST. They are designed, programmed and tested to work with 10GBase-BX compatible Brocade switches and routers. The SFP+ transceiver module supports a maximum distance of up to 40 km (24.8 mi) and delivers dependable 10 GbE connectivity over fiber cabling.

Technical Specifications:

Wavelength: 1270nmTx/1330nmRxMaximum Data Transfer Rate: 10Gbps

• **Type:** Single Mode Fiber

• Connection Type: LC Connector

Maximum Transfer Distance: 40 km (24.8 mi)

• Power Consumption: < 1.6W

DDM: Yes



Data Sheet

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

StarTech.com SFPs

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP Cables, providing the convenience and reliability you need to ensure dependable network performance.





Certifications, Reports and Compatibility













Features

- 100% BROCADE 10G-SFPP-BXU-40K COMPATIBLE: 10 Gigabit Ethernet BiDi Fiber Single Strand SFP+ designed, programmed and tested to work with compatible Brocade switches and routers to deliver dependable 10GbE connectivity
- INCREASE BANDWIDTH ON EXISTING INFRASTRUCTURE: This 10
 Gigabit Ethernet bi-directional WDM SFP+ transceiver module sends and receives over a single strand of fiber optic cable instead of two
- TECHNICAL SPECS: 10GBASE-BX-U | 10Gbps | 10G Bi-Directional Upstream | Single Mode (SMF) | LC Connector | 1270nmTx/1330nmRx | Digital Diagnostic Monitoring (DDM) | Distances up to 40km (24.8mi)
- LIFETIME WARRANTY: Backed by a lifetime warranty on the life of the module itself, not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24
- PROGRAMMED & TESTED FOR COMPATIBILITY: Compatible with Brocade routers and switches. MSA Compliant with DDM that reports the transceiver's status to most SNMP network management tools



Data Sheet

	Warranty	Lifetime
Hardware	Compatible Brand	Brocade
Performance	DDM	Yes
	Maximum Data Transfer Rate	10.00 Gbps
	Power Consumption (In Watts)	< 1.6W
Physical Characteristics	Product Height	12.600
	Product Length	0.5 in [1.4 cm]
	Product Width	58.400
	Weight of Product	24.000
Packaging Information	Package Height	31.000
	Package Length	115.000
	Package Width	90.000
	Shipping (Package) Weight	50.000

Product appearance and specifications are subject to change without notice.