

HPE JG661A Compatible QSFP+ Module - 40GBASE-LR4 - 40GbE Single Mode Fiber Optic Transceiver - 40GE Gigabit Ethernet QSFP+ - LC 10km - 1270nm to 1330nm - DDM HPE 5900AF, 12902

Product ID: JG661A-ST



The JG661A-ST is a HP JG709A compatible fiber transceiver module that has been designed, programmed and tested to work with HP brand switches and routers. It delivers dependable 40 GbE connectivity over fiber cable, for 40GBase-SR4 compliant networks, with a maximum distance of up to 300 m (984 ft).

Technical Specifications:

- **Wavelength:** 850nm
- **Maximum Data Transfer Rate:** 40 Gbps
- **Type:** Multi Mode Fiber
- **Connection Type:** MPO Connector
- **Maximum Transfer Distance:** 300 m (984 ft)
- **MTBF:** 244,610,583 hours
- **Power Consumption:** < 1.3W
- **Digital Diagnostics Monitoring (DDM):** Yes

This QSFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

StarTech.com SFPs

All StarTech.com SFP & QSFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of QSFP+ modules and direct-attach QSFP+ cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Features

- 100% HPE JG661A COMPATIBLE: Works with HPE switches like 5900AF, 12902 and others
- TECHNICAL SPECS: 40GBASE-LR4 | 40Gbps | Single Mode (SMF) | LC Connector | 1270nm to 1330nm | Digital Diagnostic Monitoring (DDM) | Distances up to 10km (6.2mi)
- TESTED FOR OEM HOST COMPATIBILITY: Hot-swappable in HPE routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- LIFETIME WARRANTY: Backed by a lifetime warranty on the life of the module itself - not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24
- WORKS WITH MSA COMPLIANT SWITCHES: Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

	Warranty	Lifetime
Hardware	Compatible Brand	HPE
Performance	Maximum Data Transfer Rate	40.00 Gbps
Physical Characteristics	Product Height	8.500
	Product Length	0.7 in [1.8 cm]
	Product Width	122.000
	Weight of Product	49.000
Packaging Information	Package Height	35.000
	Package Length	205.000
	Package Width	120.000
	Shipping (Package) Weight	60.000
What's in the Box	Included in Package	1 - QSFP+ Transceiver

Product appearance and specifications are subject to change without notice.